



Actual

**Catalog Number:** BTC0614  
**Product ID:** 7TAH006700R0069  
**UPC Number:** 78378661131  
**EAN Number:** 05414363148685  
**Status:** Active

Type BTC - Copper Single-Conductor, One-Hole Mount (Offset-Tang), Conductor Range 6 Str-14 AWG, Length 1-9/64, Width 3/8 Inch, Height 11/16 Inch, 13/64 Bolt Inch Hole

- Uniquely designed pressure bar and notched v-bottom collar provide vise-like grip between conductor and terminal.
- Made of electrolytic seamless copper. Screws are zinc-plated steel.

### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Copper Connectors
Special Features	Uniquely designed pressure bar and notched v-bottom collar provide vise-like grip between conductor and terminal.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	14 AWG-6 Str.

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	2.25x2.063x2.25
Outer Quantity	100
Outer Dimensions (inches)	10.8x5.9x2.9
Weight Uom	2.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)