



Actual

**Catalog Number:** **PC250**  
**Product ID:** 7TAA267210R0003  
**UPC Number:** 78378684971  
**Status:** Active

Copper Type PC - Two Bolt Parallel Groove Clamp for Wire Range Main: 4 Solid - 250 Stranded, Tap: 4 Solid - 250 Stranded. Hex-Head 3/8 inch Bolts. Overall Bolt Length 2-5/16 inches. Body 2 inches X 1-3/4 inches.

### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Parallel Groove Clamp
Special Features	Made of high-strength copper alloy. Hex head bolts with square shank of silicon bronze. Spring washers are also of silicon bronze. Square shank bolts prevent turning while tightening. Contour of casting permits use of socket wrench if desired. Large contact area increases conductance. Not recommended for use with aluminum conductor.
Application	Overhead Connector
Connection	Mechanical
Number Of Conductors	2
Material	Copper
Voltage Rating	35kV
Insulation	No
Conductor Range (Main/Primary)	4 Solid - 250 Stranded
Conductor Range (Tap/Secondary)	4 Solid - 250 Stranded
Bolt Size	3/8 inch

### Packaging

Inner Quantity	6
Outer Quantity	60
Outer Dimensions (inches)	19x10.2x8
Weight Uom	66.38 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)