

Login

Search...  
Advanced Search

Help

Home

- [Customer Self Service](#)
- [About Us](#)
- [Products](#)
- [Reference](#)
- [ILSCO Product Catalog](#)

## 2ACL 2 HOLE, LONG BARREL

Home > ILSCO Product Catalog > Compression > Aluminum Compression (Dual Rated) > 2ACL 2 HOLE, LONG BARREL



- Manufactured from high strength aluminum alloy and Electro-Tin plated.
- Chamfered barrel and Prefilled with DE-OX.
- UL 486A/B 90° C Listed and is CSA Certified for 600 Volts.
- If proper high voltage spacings and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Clearly marked with wire size and die index for IlSCO tools, proper number and location of crimps.
- Dual Rated for Copper and Aluminum.
- Strand configurations:
- Aluminum - Class B concentric, compressed, and unidirectional lay compact.
- Copper - Class B concentric, Class B compressed, Class C concentric.
- Range-taking when used with IDT-12-N Tool.
- Listed with IlSCO tools ILC-12, ILC-12H, ILCB-12, ILC-14, ILC-14H, IDTB-12, ILC-15, MT-25, 94285, IDT-12, IDT-12H.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools. Refer to Tool and Die Charts under Reference Tab.
- UL File E6207

Items Per Page

Compare

Bolt/Stud Size

Conductor Size

Mounting Hole Spacing

Compare	Item ID	Conductor Size	Expanded Conductor Range	Bolt/Stud Size	Mounting Hole Spacing	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Index Number	Die Catalog Number	QTY
<input type="checkbox"/>	2ACL-1/0	1/0 AWG	1/0-1 AWG	3/8	1	1.8750	0.8750	1.2500	1.3125	3.4690	TAN	8	ILD-8	0
<input type="checkbox"/>	2ACN-1/0	1/0 AWG	1/0-1 AWG	1/2	1-3/4	3.0000	0.8750	1.1250	1.1850	4.6250	TAN	8	ILD-8	0
<input type="checkbox"/>	2ACL-2/0	2/0 AWG	2/0-1 AWG	1/2	1-3/4	3.3750	0.9688	1.030	1.0925	5.0000	OLIVE	10	ILD-10	0
<input type="checkbox"/>	2ACL-3/0	3/0 AWG	3/0-1 AWG	1/2	1-3/4	3.3750	1.0625	1.3600	1.4225	5.1563	RUBY	10	ILD-10	0
<input type="checkbox"/>	2ACL-4/0	4/0 AWG	4/0-1 AWG	1/2	1-3/4	3.3750	1.1250	1.8130	1.8755	5.6250	WHITE	12	ILD-12	0
<input type="checkbox"/>	2ACL-250	250 kcmil	250 kcmil - 1/0 AWG	1/2	1-3/4	3.3750	1.3281	1.7890	1.8515	5.7500	RED	13	ILD-13	0
<input type="checkbox"/>	2ACL-300	300 kcmil	300 kcmil - 2/0 AWG	1/2	1-3/4	3.3750	1.4375	2.0310	2.0935	5.9375	BLUE	14	ILD-14	1
<input type="checkbox"/>	2ACL-350	350 kcmil	350 kcmil - 3/0 AWG	1/2	1-3/4	3.3750	1.5630	2.0310	2.0935	5.9688	BROWN	14	ILD-14	1
<input type="checkbox"/>	2ACL-400	400 kcmil	400 kcmil - 4/0 AWG	1/2	1-3/4	3.3750	1.6250	2.6550	2.7175	6.6875	GREEN	16	ILD-16	1
<input type="checkbox"/>	2ACL-500	500 kcmil	500 kcmil - 4/0 AWG	1/2	1-3/4	3.3750	1.8130	2.6610	2.8125	6.8130	PINK	16A	ILD-16A	1
<input type="checkbox"/>	2ACL-600	600 kcmil	600 kcmil - 250 kcmil	1/2	1-3/4	3.3750	1.9380	2.7190	2.7815	6.7500	BLACK	17	ILD-17	1
<input type="checkbox"/>	2ACL-700	700 kcmil	700 kcmil - 350 kcmil	1/2	1-3/4	3.3750	2.0625	2.8130	2.8755	6.9375	PURPLE	17	ILD-17	1
<input type="checkbox"/>	2ACL-750	750 kcmil	750 kcmil - 500 kcmil	1/2	1-3/4	3.3750	2.0630	2.7050	2.7675	6.9375	YELLOW	18	ILD-18	1
<input type="checkbox"/>	2ACL-1000	1000 kcmil	1000 kcmil - 750 kcmil	1/2	1-3/4	3.3750	2.5000	3.3600	3.4225	7.7500	BROWN	20		1

[Contact Us](#) [Privacy Policy](#)

©1991-2013 [CDI Technology](#) All Rights Reserved

ILSCO  
4730 MADISON ROAD  
CINCINNATI, OH 45227  
513-533-8200  
800-776-9775