

Login

Search...  
 Advanced Search

Help

Home

- [Customer Self Service](#)
- [About Us](#)
- [Products](#)
- [Reference](#)
- [ILSCO Product Catalog](#)

ACO AL OFFSET PIN

Home > ILSCO Product Catalog > Compression > Pin Terminals > ACO AL OFFSET PIN



- UL486A/B Listed and CSA Certified.
- Rated for 600 Volts and 90° C.
- Dual Rated for Aluminum and Copper Conductor.
- Stranded Class B & C concentric, compressed and unidirectional lay compact
- Rated for full ampacity of incoming conductor.
- Manufactured from high strength aluminum alloy.
- Pin is knurled and off center.
- Chamfered barrel and prefilled with De-Ox.
- Clearly marked with conductor size and die index.
- Marked with number and location of crimps and Color Coded.
- All supplied with insulating cover except ACO-1000.
- ACO-1000 is range taking.
- ACO-1000 must be applied with Dieless Tools Only.
- Refer to Tool & Die Charts under Reference Tab for listed Tools.
- UL File # E62525

Items Per Page Compare

Compare	Item ID	Conductor Size	Die Index Number	Color Code	Pin Diameter	Pin Length	Barrel Length	Cover Length	Approximate Pin Size	Standard Package Quantity	NAED/UPC Number
<input type="checkbox"/>	ACO-2/0	2/0 AWG	12	WHITE	.3300	.8400	1.3700	2.000	#1	10	0783669009507
<input type="checkbox"/>	ACO-3/0	3/0 AWG	12	WHITE	.3700	1.2200	1.3700	2.000	1/0	10	0783669009521
<input type="checkbox"/>	ACO-4/0	4/0 AWG	12	WHITE	.4200	1.2200	1.3700	2.000	2/0	10	0783669009545
<input type="checkbox"/>	ACO-250	250 kcmil	14	BROWN	.4700	1.2200	1.4100	2.250	3/0	10	0783669009569
<input type="checkbox"/>	ACO-300	300 kcmil	14	BROWN	.5300	1.3400	1.4100	2.250	4/0	10	0783669009576
<input type="checkbox"/>	ACO-350	350 kcmil	14	BROWN	.5700	1.3400	1.4100	2.250	250 kcmil	10	0783669009583
<input type="checkbox"/>	ACO-90-350	350 kcmil	14	BROWN	.5700	1.3400	1.4100	2.250	250 kcmil	6	0783669009675
<input type="checkbox"/>	ACO-500	500 kcmil	16A	PINK	.6800	1.6000	2.0300	3.250	350 kcmil	10	0783669009606
<input type="checkbox"/>	ACO-90-500	500 kcmil	16A	PINK	.6800	1.6000	2.0300	3.250	350 kcmil	3	0783669009682
<input type="checkbox"/>	ACO-600	600 kcmil	18	YELLOW	.7300	1.6400	2.0300	3.250	400 kcmil	3	0783669009620
<input type="checkbox"/>	ACO-750	700 kcmil, 750 kcmil	18	YELLOW	.8100	1.7600	2.0300	3.250	500 kcmil	3	0783669009644
<input type="checkbox"/>	ACO-1000	1000 kcmil-750 kcmil	N/A	N/A	.9000	2.0000	2.0300	N/A	600 kcmil	3	0783669009651