

Login

Search...
Advanced Search

Help

Home

- [Customer Self Service](#)
- [About Us](#)
- [Products](#)
- [Reference](#)
- [ILSCO Product Catalog](#)

CLND 2 HOLE LONG BARREL

Home > ILSCO Product Catalog > Compression > New Copper Compression > CLND 2 HOLE LONG BARREL



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Long barrel length with chamfered entry.
- Color Coded.
- UL 486A/B 90° C Listed and CSA Certified for 600 Volts.
- 1/0 AWG - 8 AWG UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded Conductor Range with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools.
- Refer to Tool and Die Charts under reference tab.
- UL File E6207

Items Per Page

Compare

Bolt/Stud Size

Conductor Size

Mounting Hole Spacing

Compare	Item ID	Conductor Size	Alternate Conductor Size	Expanded Conductor Range	Bolt/Stud Size	Mounting Hole Diameter	Mounting Hole Spacing	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Di Ind Num
<input type="checkbox"/>	CLND-2-38-1	#2 AWG		2-6 AWG	3/8	0.406	1	1.9370	0.5990	1.1250	1.1870	3.3480	BROWN	I-3
<input type="checkbox"/>	CLND-2-38-134	#2 AWG		2-6 AWG	3/8	0.406	1-3/4	2.6250	0.5990	1.1250	1.1870	4.0360	BROWN	I-3
<input type="checkbox"/>	CLND-2-12-134	#2 AWG		2-6 AWG	1/2	0.562	1-3/4	3.0000	0.5990	1.1250	1.1870	4.4110	BROWN	I-3
<input type="checkbox"/>	CLND-1-14-58	#1 AWG	#2 FLEX	1-6 AWG	1/4	0.281	5/8	1.4370	0.6730	1.3750	1.4370	3.1420	GREEN	I-3
<input type="checkbox"/>	CLND-1-14-34	#1 AWG	#2 FLEX	1-6 AWG	1/4	0.281	3/4	1.4370	0.6730	1.3750	1.4370	3.1420	GREEN	I-3
<input type="checkbox"/>	CLND-1-14-1	#1 AWG	#2 FLEX	1-6 AWG	1/4	0.281	1	1.6870	0.6730	1.3750	1.4370	3.3920	GREEN	I-3
<input type="checkbox"/>	CLND-1-516-78	#1 AWG	#2 FLEX	1-6 AWG	5/16	0.343	7/8	1.6870	0.6730	1.3750	1.4370	3.3920	GREEN	I-3
<input type="checkbox"/>	CLND-1-516-1	#1 AWG	#2 FLEX	1-6 AWG	5/16	0.343	1	1.9370	0.6730	1.3750	1.4370	3.6420	GREEN	I-3
<input type="checkbox"/>	CLND-1-38-1	#1 AWG	#2 FLEX	1-6 AWG	3/8	0.406	1	1.9370	0.6730	1.3750	1.4370	3.6420	GREEN	I-3
<input type="checkbox"/>	CLND-1-12-134	#1 AWG	#2 FLEX	1-6 AWG	1/2	0.562	1-3/4	3.0000	0.6730	1.3750	1.4370	4.7050	GREEN	I-3
<input type="checkbox"/>	CLND-1/0-14-58	1/0 AWG	#1 FLEX	1/0-6 AWG	1/4	0.281	5/8	1.4370	0.7380	1.5000	1.5620	3.2930	PINK	I-4
<input type="checkbox"/>	CLND-1/0-14-34	1/0 AWG	#1 FLEX	1/0-6 AWG	1/4	0.281	3/4	1.4370	0.7380	1.5000	1.5620	3.2930	PINK	I-4
<input type="checkbox"/>	CLND-1/0-14-1	1/0 AWG	#1 FLEX	1/0-6 AWG	1/4	0.281	1	1.6870	0.7380	1.5000	1.5620	3.5430	PINK	I-4
<input type="checkbox"/>	CLND-1/0-516-34	1/0 AWG	#1 FLEX	1/0-6 AWG	5/16	0.343	3/4	1.6870	0.7380	1.5000	1.5620	3.5430	PINK	I-4
<input type="checkbox"/>	CLND-1/0-516-78	1/0 AWG	#1 FLEX	1/0-6 AWG	5/16	0.343	7/8	1.6870	0.7380	1.5000	1.5620	3.5430	PINK	I-4
<input type="checkbox"/>	CLND-1/0-516-1	1/0 AWG	#1 FLEX	1/0-6 AWG	5/16	0.343	1	1.9370	0.7380	1.5000	1.5620	3.7930	PINK	I-4
<input type="checkbox"/>	CLND-1/0-38-1	1/0 AWG	#1 FLEX	1/0-6 AWG	3/8	0.406	1	1.9370	0.7380	1.5000	1.5620	3.7930	PINK	I-4
<input type="checkbox"/>	CLND-1/0-38-134	1/0 AWG	#1 FLEX	1/0-6 AWG	3/8	0.406	1-3/4	2.6250	0.7380	1.5000	1.5620	4.4810	PINK	I-4
<input type="checkbox"/>	CLND-1/0-12-1	1/0 AWG	#1 FLEX	1/0-6 AWG	1/2	0.562	1	2.1250	0.7380	1.5000	1.5620	3.9810	PINK	I-4
<input type="checkbox"/>	CLND-1/0-12-134	1/0 AWG	#1 FLEX	1/0-6 AWG	1/2	0.562	1-3/4	3.0000	0.7380	1.5000	1.5620	4.8560	PINK	I-4

[Contact Us](#) [Privacy Policy](#) [Terms And Conditions](#)

©1991-2013 [CDI Technology](#) All Rights Reserved

UTILCO
4730 MADISON ROAD
CINCINNATI, OH 45227
513-533-6200
800-776-9775