



Login

Search...  

Advanced Search

Help

Home

-  [Customer Self Service](#)
-  [About Us](#)
-  [Products](#)
-  [Reference](#)
-  [ILSCO Product Catalog](#)

CLND 2 HOLE LONG BARREL

Home > ILSCO Product Catalog > Compression > New Copper Compression > CLND 2 HOLE LONG BARREL



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Long barrel length with chamfered entry.
- Color Coded.
- UL 486A/B 90° C Listed and CSA Certified for 600 Volts.
- 1/0 AWG - 8 AWG UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded Conductor Range with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools.
- Refer to Tool and Die Charts under reference tab.
- UL File E6207

Items Per Page

Compare

Bolt/Stud Size

Conductor Size

Mounting Hole Spacing

Compare	Item ID	Conductor Size	Alternate Conductor Size	Expanded Conductor Range	Bolt/Stud Size	Mounting Hole Diameter	Mounting Hole Spacing	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Inde Numb
<input type="checkbox"/>	CLND-4-14-58	#4 AWG		4-6 AWG	1/4	0.281	5/8	1.4370	0.4860	1.1250	1.1870	2.7960	GRAY	I-29
<input type="checkbox"/>	CLND-4-14-34	#4 AWG		4-6 AWG	1/4	0.281	3/4	1.4370	0.4860	1.1250	1.1870	2.7960	GRAY	I-29
<input type="checkbox"/>	CLND-4-516-34	#4 AWG		4-6 AWG	5/16	0.343	3/4	1.6870	.4860	1.1250	1.1875	3.0460	GRAY	I-29
<input type="checkbox"/>	CLND-4-38-1	#4 AWG		4-6 AWG	3/8	0.406	1	1.9370	0.4860	1.1250	1.1870	3.2960	GRAY	I-29
<input type="checkbox"/>	CLND-4-12-134	#4 AWG		4-6 AWG	1/2	0.562	1-3/4	3.0000	0.4860	1.1250	1.1870	4.3590	GRAY	I-29
<input type="checkbox"/>	CLND-3-14-58	#3 AWG	#4 FLEX	3-6 AWG	1/4	0.281	5/8	1.4370	0.5320	1.1250	1.1870	2.8170	WHITE	I-29
<input type="checkbox"/>	CLND-3-14-34	#3 AWG	#4 FLEX	3-6 AWG	1/4	0.281	3/4	1.4370	0.5320	1.1250	1.1870	2.8170	WHITE	I-29
<input type="checkbox"/>	CLND-3-516-58	#3 AWG	#4 FLEX	3-6 AWG	5/16	0.343	5/8	1.4370	0.5320	1.1250	1.1870	2.8170	WHITE	I-29
<input type="checkbox"/>	CLND-3-516-1	#3 AWG	#4 FLEX	3-6 AWG	5/16	0.343	1	1.9370	0.5320	1.1250	1.1870	3.3170	WHITE	I-29
<input type="checkbox"/>	CLND-3-38-34	#3 AWG	#4 FLEX	3-6 AWG	3/8	0.406	3/4	1.6870	0.5320	1.1250	1.1870	3.0670	WHITE	I-29
<input type="checkbox"/>	CLND-3-38-1	#3 AWG	#4 FLEX	3-6 AWG	3/8	0.406	1	1.9370	0.5320	1.1250	1.1870	3.3170	WHITE	I-29
<input type="checkbox"/>	CLND-3-12-134	#3 AWG	#4 FLEX	3-6 AWG	1/2	0.562	1-3/4	3.0000	0.5320	1.1250	1.1870	4.3800	WHITE	I-29
<input type="checkbox"/>	CLND-2-10-34	#2 AWG		2-6 AWG	10	0.219	3/4	1.4370	0.5990	1.1250	1.1870	2.8480	BROWN	I-33
<input type="checkbox"/>	CLND-2-14-58	#2 AWG		2-6 AWG	1/4	0.281	5/8	1.4370	0.5990	1.1250	1.1870	2.8480	BROWN	I-33
<input type="checkbox"/>	CLND-2-14-34	#2 AWG		2-6 AWG	1/4	0.281	3/4	1.4370	0.5990	1.1250	1.1870	2.8480	BROWN	I-33
<input type="checkbox"/>	CLND-2-14-1	#2 AWG		2-6 AWG	1/4	0.281	1	1.6870	0.5990	1.1250	1.1870	3.0980	BROWN	I-33
<input type="checkbox"/>	CLND-2-516-34	#2 AWG		2-6 AWG	5/16	0.343	3/4	1.6870	0.5990	1.1250	1.1870	3.0980	BROWN	I-33
<input type="checkbox"/>	CLND-2-516-1	#2 AWG		2-6 AWG	5/16	0.343	1	1.9370	0.5990	1.1250	1.1870	3.3480	BROWN	I-33
<input type="checkbox"/>	CLND-2-38-34	#2 AWG		2-6 AWG	3/8	0.406	3/4	1.6870	0.5990	1.1250	1.1870	3.0980	BROWN	I-33
<input type="checkbox"/>	CLND-2-38-78	#2 AWG		2-6 AWG	3/8	0.406	7/8	1.9370	0.5990	1.1250	1.1870	3.3480	BROWN	I-33

[Contact Us](#) [Privacy Policy](#) [Terms And Conditions](#)

©1991-2013 [CDI Technology](#) All Rights Reserved

ILSCO
 4730 MADISON ROAD
 CINCINNATI, OH 45227
 513-533-6200
 800-776-9775