

2 HOLE LONG BARREL



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Long barrel length with chamfered entry.
- Color Coded.
- UL 486A, 90° C Listed and CSA Certified for 600 Volts...
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Range-taking with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools.
- Refer to Tool and Die Charts under reference tab.
- UL File E6207

Item ID	Conductor Size	Alternate Conductor Size	Expanded Conductor Range	Bolt/Stud Size	Mounting Hole Diameter	Mounting Hole Spacing	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Index Number	Die Catalog Number	Outside Diameter	Inside Diameter	Standard Package Quantity	NAE/JPC Number
CLND-4-14-58	#4, AWG	#6 FLEX	4-6 AWG	1/4	0.281	5/8	1.4370	0.4860	1.1250	1.187	2.7960	Gray	I-29	ILD-29	0.3430	0.2500	50	78366963078