

Login

Search...
Advanced Search

Visit our Other sites: FTZ | ILSCO Extrusion

Help



Home

- [About Us](#)
- [Products](#)
- [Reference](#)
- [ILSCO Product Catalog](#)

CLND 2 HOLE LONG BARREL

Home > ILSCO Product Catalog > Compression > New Copper Compression > CLND 2 HOLE LONG BARREL



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Long barrel length with chamfered entry.
- Color Coded.
- UL 486A/B 90° C Listed and CSA Certified for 600 Volts.
- 1/0 AWG - 8 AWG UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded Conductor Range with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools.
- Refer to Tool and Die Charts under reference tab.
- UL File E6207

Items Per Page

Compare

Bolt/Stud Size

Conductor Size

Mounting Hole Spacing

Compare	Item ID	Conductor Size	Alternate Conductor Size	Expanded Conductor Range	Bolt/Stud Size	Mounting Hole Diameter	Mounting Hole Spacing	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Index Number
<input type="checkbox"/>	CLND-8-10-58	#8 AWG	#8 FLEX		10	0.219	5/8	1.2500	0.3740	0.8120	0.8740	2.2570	RED	I-21
<input type="checkbox"/>	CLND-8-10-34	#8 AWG	#8 FLEX		10	0.219	3/4	1.4370	0.3740	0.8120	0.8740	2.4440	RED	I-21
<input type="checkbox"/>	CLND-8-14-58	#8 AWG	#8 FLEX		1/4	0.281	5/8	1.4370	0.3740	0.8120	0.8740	2.4440	RED	I-21
<input type="checkbox"/>	CLND-8-14-34	#8 AWG	#8 FLEX		1/4	0.281	3/4	1.4370	0.3740	0.8120	0.8740	2.4440	RED	I-21
<input type="checkbox"/>	CLND-8-38-1	#8 AWG	#8 FLEX		3/8	0.406	1	1.9370	0.3740	0.8120	0.8740	2.9440	RED	I-21
<input type="checkbox"/>	CLND-6-10-12	#6 AWG	#6 FLEX		10	0.219	1/2	1.2500	0.4110	1.1250	1.1870	2.5700	BLUE	I-24
<input type="checkbox"/>	CLND-6-10-58	#6 AWG	#6 FLEX		10	0.219	5/8	1.2500	0.4110	1.1250	1.1870	2.5700	BLUE	I-24
<input type="checkbox"/>	CLND-6-10-1116	#6 AWG	#6 FLEX		10	0.219	11/16	1.2500	0.4110	1.1250	1.1870	2.5700	BLUE	I-24
<input type="checkbox"/>	CLND-6-10-34	#6 AWG	#6 FLEX		10	0.219	3/4	1.4370	0.4110	1.1250	1.1870	2.7570	BLUE	I-24
<input type="checkbox"/>	CLND-6-14-12	#6 AWG	#6 FLEX		1/4	0.281	1/2	1.2500	0.4110	1.1250	1.1870	2.5700	BLUE	I-24
<input type="checkbox"/>	CLND-6-14-58	#6 AWG	#6 FLEX		1/4	0.281	5/8	1.4370	0.4110	1.1250	1.1870	2.7570	BLUE	I-24
<input type="checkbox"/>	CLND-6-14-34	#6 AWG	#6 FLEX		1/4	0.281	3/4	1.4370	0.4110	1.1250	1.1870	2.7570	BLUE	I-24
<input type="checkbox"/>	CLND-6-14-1	#6 AWG	#6 FLEX		1/4	0.281	1	1.6870	0.4110	1.1250	1.1870	3.0070	BLUE	I-24
<input type="checkbox"/>	CLND-6-38-34	#6 AWG	#6 FLEX		3/8	0.406	3/4	1.6870	0.4110	1.1250	1.1870	3.0070	BLUE	I-24
<input type="checkbox"/>	CLND-6-38-1	#6 AWG	#6 FLEX		3/8	0.406	1	1.9370	0.4110	1.1250	1.1870	3.2570	BLUE	I-24
<input type="checkbox"/>	CLND-6-38-134	#6 AWG	#6 FLEX		3/8	0.406	1-3/4	2.6250	0.4110	1.1250	1.1870	3.9450	BLUE	I-24
<input type="checkbox"/>	CLND-6-12-134	#6 AWG	#6 FLEX		1/2	0.562	1-3/4	3.0000	0.4110	1.1250	1.1870	4.3200	BLUE	I-24
<input type="checkbox"/>	CLND-4-10-58	#4 AWG		4-6 AWG	10	0.219	5/8	1.2500	0.4860	1.1250	1.1870	2.6090	GRAY	I-29
<input type="checkbox"/>	CLND-4-10-34	#4 AWG		4-6 AWG	10	0.219	3/4	1.4370	0.4860	1.1250	1.1870	2.7960	GRAY	I-29
<input type="checkbox"/>	CLND-4-10-1	#4 AWG		4-6 AWG	10	0.219	1	1.6870	0.4860	1.1250	1.1870	3.0460	GRAY	I-29

[Contact Us](#) [Privacy Policy](#) [Terms And Conditions](#)

©1991-2013 [CDI Technology](#) All Rights Reserved

ILSCO
4730 MADISON ROAD
CINCINNATI, OH 45227
513-533-6200
800-776-9775