

Login

Search...
Advanced Search

Visit our Other sites: FTZ | ILSCO Extrusion

Help



Home

- [About Us](#)
- [Products](#)
- [Reference](#)
- [ILSCO Product Catalog](#)

CLWD 2 HOLE LONG W/SIGHT

Home > ILSCO Product Catalog > Compression > New Copper Compression > CLWD 2 HOLE LONG W/SIGHT



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Long barrel length with chamfered entry.
- Sight hole and chamfered barrel for visual inspection of proper cable insertion.
- Color Coded.
- UL 486A/B 90° C Listed and CSA Certified for 600 Volts.
- 1/0 AWG - 8 AWG UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded wire size with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- Strand configurations:
- Copper - Class B concentric, Class B compressed, Class C concentric.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools.
- Refer to Tool and Die Charts under reference tab.
- UL File E6207

Items Per Page

Compare

Bolt/Stud Size

Conductor Size

Mounting Hole Spacing

Compare	Item ID	Conductor Size	Alternate Conductor Size	Expanded Conductor Range	Bolt/Stud Size	Mounting Hole Diameter	Mounting Hole Spacing	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	I In Nu
<input type="checkbox"/>	CLWD-1/0-14-34	1/0 AWG	#1 FLEX	1/0-6 AWG	1/4	0.281	3/4	1.4370	0.7380	1.5000	1.5620	3.2930	PINK	I-
<input type="checkbox"/>	CLWD-1/0-14-1	1/0 AWG	#1 FLEX	1/0-6 AWG	1/4	0.281	1	1.6870	0.7380	1.5000	1.5620	3.5430	PINK	I-
<input type="checkbox"/>	CLWD-1/0-516-34	1/0 AWG	#1 FLEX	1/0-6 AWG	5/16	0.343	3/4	1.6870	0.7380	1.5000	1.5620	3.5430	PINK	I-
<input type="checkbox"/>	CLWD-1/0-516-78	1/0 AWG	#1 FLEX	1/0-6 AWG	5/16	0.343	7/8	1.6870	0.7380	1.5000	1.5620	3.5430	PINK	I-
<input type="checkbox"/>	CLWD-1/0-516-1	1/0 AWG	#1 FLEX	1/0-6 AWG	5/16	0.343	1	1.9370	0.7380	1.5000	1.5620	3.7930	PINK	I-
<input type="checkbox"/>	CLWD-1/0-38-34	1/0 AWG	#1 FLEX	1/0-6 AWG	3/8	0.406	3/4	1.6870	0.7380	1.5000	1.5620	3.5430	PINK	I-
<input type="checkbox"/>	CLWD-1/0-38-1	1/0 AWG	#1 FLEX	1/0-6 AWG	3/8	0.406	1	1.9370	0.7380	1.5000	1.5620	3.7930	PINK	I-
<input type="checkbox"/>	CLWD-1/0-38-134	1/0 AWG	#1 FLEX	1/0-6 AWG	3/8	0.406	1-3/4	2.6250	0.7380	1.5000	1.5620	4.4810	PINK	I-
<input type="checkbox"/>	CLWD-1/0-12-1	1/0 AWG	#1 FLEX	1/0-6 AWG	1/2	0.562	1	2.1250	0.7380	1.5000	1.5620	3.9810	PINK	I-
<input type="checkbox"/>	CLWD-1/0-12-134	1/0 AWG	#1 FLEX	1/0-6 AWG	1/2	0.562	1-3/4	3.0000	0.7380	1.5000	1.5620	4.8560	PINK	I-
<input type="checkbox"/>	CLWD-2/0-14-58	2/0 AWG	1/0 FLEX	2/0-4 AWG	1/4	0.281	5/8	1.4370	0.8110	1.5000	1.5620	3.3330	BLACK	I-
<input type="checkbox"/>	CLWD-2/0-14-34	2/0 AWG	1/0 FLEX	2/0-4 AWG	1/4	0.281	3/4	1.4370	0.8110	1.5000	1.5620	3.3330	BLACK	I-
<input type="checkbox"/>	CLWD-2/0-14-1	2/0 AWG	1/0 FLEX	2/0-4 AWG	1/4	0.281	1	1.6870	0.8110	1.5000	1.5620	3.5830	BLACK	I-
<input type="checkbox"/>	CLWD-2/0-516-1	2/0 AWG	1/0 FLEX	2/0-4 AWG	5/16	0.343	1	1.9370	0.8110	1.5000	1.5620	3.8330	BLACK	I-
<input type="checkbox"/>	CLWD-2/0-38-1	2/0 AWG	1/0 FLEX	2/0-4 AWG	3/8	0.406	1	1.9370	0.8110	1.5000	1.5620	3.8330	BLACK	I-
<input type="checkbox"/>	CLWD-2/0-38-134	2/0 AWG	1/0 FLEX	2/0-4 AWG	3/8	0.406	1-3/4	2.6250	0.8110	1.5000	1.5620	4.5210	BLACK	I-
<input type="checkbox"/>	CLWD-2/0-12-1	2/0 AWG	1/0 FLEX	2/0-4 AWG	1/2	0.562	1	2.1250	0.8110	1.5000	1.5620	4.0210	BLACK	I-
<input type="checkbox"/>	CLWD-2/0-12-134	2/0 AWG	1/0 FLEX	2/0-4 AWG	1/2	0.562	1-3/4	3.0000	0.8110	1.5000	1.5620	4.8960	BLACK	I-
<input type="checkbox"/>	CLWD-3/0-14-58	3/0 AWG	2/0 FLEX	3/0-2 AWG	1/4	0.281	5/8	1.4370	0.8850	1.5000	1.5620	3.3760	ORANGE	I-
<input type="checkbox"/>	CLWD-3/0-14-34	3/0 AWG	2/0 FLEX	3/0-2 AWG	1/4	0.281	3/4	1.4370	0.8850	1.5000	1.5620	3.3760	ORANGE	I-

[Contact Us](#) [Privacy Policy](#) [Terms And Conditions](#)

©1991-2013 [CDI Technology](#) All Rights Reserved

ILSCO
4730 MADISON ROAD
CINCINNATI, OH 45227
513-533-6200
800-776-9775