

Login

Search...  
Advanced Search

Visit our Other sites: FTZ | ILSCO Extrusion

Help



Home

- [About Us](#)
- [Products](#)
- [Reference](#)
- [ILSCO Product Catalog](#)

### CLWD 2 HOLE LONG W/SIGHT

Home > ILSCO Product Catalog > Compression > New Copper Compression > CLWD 2 HOLE LONG W/SIGHT



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Long barrel length with chamfered entry.
- Sight hole and chamfered barrel for visual inspection of proper cable insertion.
- Color Coded.
- UL 486A/B 90° C Listed and CSA Certified for 600 Volts.
- 1/0 AWG - 8 AWG UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded wire size with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- Strand configurations.
- Copper - Class B concentric, Class B compressed, Class C concentric.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools.
- Refer to Tool and Die Charts under reference tab.
- UL File E6207

Items Per Page

Compare

Bolt/Stud Size

Conductor Size

Mounting Hole Spacing

Compare	Item ID	Conductor Size	Alternate Conductor Size	Expanded Conductor Range	Bolt/Stud Size	Mounting Hole Diameter	Mounting Hole Spacing	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Ind Numt
<input type="checkbox"/>	CLWD-4-10-34	#4 AWG		4-6 AWG	10	0.219	3/4	1.4370	0.4860	1.1250	1.1870	2.7960	GRAY	I-25
<input type="checkbox"/>	CLWD-4-10-1	#4 AWG		4-6 AWG	10	0.219	1	1.6870	0.4860	1.1250	1.1870	3.0460	GRAY	I-25
<input type="checkbox"/>	CLWD-4-14-58	#4 AWG		4-6 AWG	1/4	0.281	5/8	1.4370	0.4860	1.1250	1.1870	2.7960	GRAY	I-25
<input type="checkbox"/>	CLWD-4-14-34	#4 AWG		4-6 AWG	1/4	0.281	3/4	1.4370	0.4860	1.1250	1.1870	2.7960	GRAY	I-25
<input type="checkbox"/>	CLWD-4-14-1	#4 AWG		4-6 AWG	1/4	0.281	1	1.6870	0.4860	1.1250	1.1870	3.0460	GRAY	I-25
<input type="checkbox"/>	CLWD-4-516-58	#4 AWG		4-6 AWG	5/16	0.343	5/8	1.4370	0.4860	1.1250	1.1870	2.7960	GRAY	I-25
<input type="checkbox"/>	CLWD-4-516-34	#4 AWG		4-6 AWG	5/16	0.343	3/4	1.6870	0.4860	1.1250	1.1870	3.0460	GRAY	I-25
<input type="checkbox"/>	CLWD-4-516-1	#4 AWG		4-6 AWG	5/16	0.343	1	1.9370	0.4860	1.1250	1.1870	3.2960	GRAY	I-25
<input type="checkbox"/>	CLWD-4-38-34	#4 AWG		4-6 AWG	3/8	0.406	3/4	1.6870	0.4860	1.1250	1.1870	3.0460	GRAY	I-25
<input type="checkbox"/>	CLWD-4-38-1	#4 AWG		4-6 AWG	3/8	0.406	1	1.9370	0.4860	1.1250	1.1870	3.2960	GRAY	I-25
<input type="checkbox"/>	CLWD-4-12-134	#4 AWG		4-6 AWG	1/2	0.562	1-3/4	3.0000	0.4860	1.1250	1.1870	4.3590	GRAY	I-25
<input type="checkbox"/>	CLWD-3-14-58	#3 AWG	#4 FLEX	3-6 AWG	1/4	0.281	5/8	1.4370	0.5320	1.1250	1.1870	2.8170	WHITE	I-25
<input type="checkbox"/>	CLWD-3-14-34	#3 AWG	#4 FLEX	3-6 AWG	1/4	0.281	3/4	1.4370	0.5320	1.1250	1.1870	2.8170	WHITE	I-25
<input type="checkbox"/>	CLWD-3-14-1	#3 AWG	#4 FLEX	3-6 AWG	1/4	0.281	1	1.6870	0.5320	1.1250	1.1870	3.0670	WHITE	I-25
<input type="checkbox"/>	CLWD-3-516-58	#3 AWG	#4 FLEX	3-6 AWG	5/16	0.343	5/8	1.4370	0.5320	1.1250	1.1870	2.8170	WHITE	I-25
<input type="checkbox"/>	CLWD-3-516-1	#3 AWG	#4 FLEX	3-6 AWG	5/16	0.343	1	1.9370	0.5320	1.1250	1.1870	3.3170	WHITE	I-25
<input type="checkbox"/>	CLWD-3-38-34	#3 AWG	#4 FLEX	3-6 AWG	3/8	0.406	3/4	1.6870	0.5320	1.1250	1.1870	3.0670	WHITE	I-25
<input type="checkbox"/>	CLWD-3-38-1	#3 AWG	#4 FLEX	3-6 AWG	3/8	0.406	1	1.9370	0.5320	1.1250	1.1870	3.3170	WHITE	I-25
<input type="checkbox"/>	CLWD-3-12-134	#3 AWG	#4 FLEX	3-6 AWG	1/2	0.562	1-3/4	3.0000	0.5320	1.1250	1.1870	4.3800	WHITE	I-25
<input type="checkbox"/>	CLWD-2-10-34	#2 AWG		2-6 AWG	10	0.219	3/4	1.4370	0.5990	1.1250	1.1870	2.8480	BROWN	I-33

[Contact Us](#) [Privacy Policy](#)

©1991-2013 [CDI Technology](#) All Rights Reserved

ILSCO  
4730 MADISON ROAD  
CINCINNATI, OH 45227  
513-533-6200  
800-776-9775