

Login

Home

- [+ About Us](#)
- [+ Products](#)
- [+ Reference](#)
- [+ ILSCO Product Catalog](#)

CLWD 2 HOLE LONG W/SIGHT

Home > ILSCO Product Catalog > Compression > New Copper Compression > CLWD



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Long barrel length with chamfered entry.
- Sight hole and chamfered barrel for visual inspection of proper cable insertion.
- Color Coded.
- UL 486A/B 90° C Listed and CSA Certified for 600 Volts.
- 1/0 AWG - 8 AWG UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacing and insulation techniques are used, may be used for hi to 35KV.
- Expanded wire size with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- Strand configurations:
 - Copper - Class B concentric, Class B compressed, Class C concentric.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers'
- Refer to Tool and Die Charts under reference tab.
- UL File E6207

Items Per Page

Compare

Bolt/Stud Size

Conductor Size

Mounting Hole Spacing

Compare	Item ID	Conductor Size	Alternate Conductor Size	Expanded Conductor Range	Bolt/Stud Size	Mount Hole Diame
<input type="checkbox"/>	CLWD-8-10-58	#8 AWG	#8 FLEX		10	0.21'
<input type="checkbox"/>	CLWD-8-10-34	#8 AWG	#8 FLEX		10	0.21'
<input type="checkbox"/>	CLWD-8-14-58	#8 AWG	#8 FLEX		1/4	0.28
<input type="checkbox"/>	CLWD-8-14-34	#8 AWG	#8 FLEX		1/4	0.28
<input type="checkbox"/>	CLWD-8-38-1	#8 AWG	#8 FLEX		3/8	0.40
<input type="checkbox"/>	CLWD-6-10-12	#6 AWG	#6 FLEX		10	0.21'
<input type="checkbox"/>	CLWD-6-10-58	#6 AWG	#6 FLEX		10	0.21'