

Login

Search...  
 Advanced Search 

Visit our Other sites: [FTZ](#) | [ILSCO Extrusion](#)

Help



Home

- [About Us](#)
- [Products](#)
- [Reference](#)
- [ILSCO Product Catalog](#)

CPM AL/CU PIN

Home > ILSCO Product Catalog > Compression > Pin Terminals > CPM AL/CU PIN



- UL486A/B Listed and CSA Certified.
- Rated for 600 Volts and 90° C.
- Dual Rated for Aluminum and Copper Conductor.
- Stranded Class B & C concentric, compressed and unidirectional lay compact.
- Rated for full ampacity of incoming conductor.
- Barrel manufactured from high strength aluminum alloy.
- Pigtail manufactured from high conductivity copper.
- Chamfered barrel and prefilled with De-Ox.
- Clearly marked with conductor size and die index.
- Marked with number and location of crimps and Color Coded.
- All supplied with insulating cover.
- Dieless crimp tools must NOT be used to crimp CPM/CPML Adaptors.
- Refer to Tool & Die Charts under Reference Tab for listed Tools.
- UL File # E62525

Items Per Page

Compare

Compare	Item ID	Conductor Size	Color Code	Die Index Number	Pin Diameter	Pin Length	Barrel Length	Cover Length	Copper Pin Size	Standard Package Quantity	NAED/UPC Number
<input type="checkbox"/>	CPM-6	6 AWG	ORANGE	9	.128	.875	1.2500	1.687	#8	25	0783669008401
<input type="checkbox"/>	CPM-4	4 AWG	ORANGE	9	.184	.875	1.2500	1.687	#6	25	0783669008425
<input type="checkbox"/>	CPM-2	2 AWG	ORANGE	9	.232	.875	1.3440	1.687	#4	25	0783669008449
<input type="checkbox"/>	CPM-1	1 AWG	ORANGE	9	.258	1.000	1.3440	1.687	#3	10	0783669008463
<input type="checkbox"/>	CPM-1/0	1/0 AWG	WHITE	12	.292	1.250	1.5940	2.093	#2	10	0783669008487
<input type="checkbox"/>	CPM-2/0	2/0 AWG	WHITE	12	.332	1.250	1.5940	2.093	#1	10	0783669008500
<input type="checkbox"/>	CPM-3/0	3/0 AWG	WHITE	12	.373	1.3750	1.8750	2.093	1/0	10	0783669008524
<input type="checkbox"/>	CPM-4/0	4/0 AWG	WHITE	12	.418	1.3550	1.8450	2.093	2/0	10	0783669008548
<input type="checkbox"/>	CPM-250	250 kcmil	BROWN	14	.470	1.500	1.9380	2.846	3/0	10	0783669008562
<input type="checkbox"/>	CPM-300	300 kcmil	BROWN	14	.528	1.625	2.0620	2.846	4/0	10	0783669008586
<input type="checkbox"/>	CPM-350	350 kcmil	BROWN	14	.528	1.6170	2.0960	2.846	4/0	10	0783669008609
<input type="checkbox"/>	CPM-400	400 kcmil	PINK	16A	.575	1.875	2.0870	2.406	250	10	0783669008623
<input type="checkbox"/>	CPM-500	500 kcmil	PINK	16A	.681	1.875	2.0870	2.406	350	10	0783669008647
<input type="checkbox"/>	CPML-500	500 kcmil	PINK	16A	.681	3.000	2.0870	2.406	350	10	0783669008708
<input type="checkbox"/>	CPM-600	600 kcmil	YELLOW	18	.681	1.8750	2.7500	3.093	350	3	0783669008661
<input type="checkbox"/>	CPML-600	600 kcmil	YELLOW	18	.681	3.000	2.6250	3.093	350	3	0783669008913
<input type="checkbox"/>	CPM-750	700 kcmil, 750 kcmil	YELLOW	18	.814	2.0000	2.7500	3.093	500	3	0783669008685
<input type="checkbox"/>	CPML-750	700 kcmil, 750 kcmil	YELLOW	18	.814	3.000	2.6250	3.093	500	3	0783669008722