

Login

Search...
Advanced Search

Visit our Other sites: FTZ | ILSCO Extrusion

Help



Home

- [About Us](#)
- [Products](#)
- [Reference](#)
- [ILSCO Product Catalog](#)

CSWS 1 HOLE SHORT W/SIGHT

Home > ILSCO Product Catalog > Compression > New Copper Compression > CSWS 1 HOLE SHORT W/SIGHT



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Standard barrel length with chamfered entry.
- Sight hole and chamfered barrel for visual inspection of proper cable insertion.
- Color Coded.
- UL 486A/B 90° C Listed and CSA Certified for 600 Volts.
- 1/0 AWG - 8 AWG UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded wire size with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- Strand configurations:
- Copper - Class B concentric, Class B compressed, Class C concentric.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools.
- Refer to Tool and Die Charts under reference tab.
- UL File E6207

Items Per Page

Compare

Bolt/Stud Size

Conductor Size

Compare	Item ID	Bolt/Stud Size	Conductor Size	Alternate Conductor Size	Expanded Conductor Range	Mounting Hole Diameter	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Index Number	Die Catalog Number	O
<input type="checkbox"/>	CSWS-8-10	10	#8 AWG	#8 FLEX		0.219	0.5620	0.3740	0.5000	0.5620	1.2570	RED	I-21	ILD-21	(
<input type="checkbox"/>	CSWS-8-14	1/4	#8 AWG	#8 FLEX		0.281	0.6800	0.3740	0.5000	0.5620	1.3750	RED	I-21	ILD-21	(
<input type="checkbox"/>	CSWS-8-516	5/16	#8 AWG	#8 FLEX		0.343	0.8750	0.3740	0.5000	0.5620	1.5700	RED	I-21	ILD-21	(
<input type="checkbox"/>	CSWS-8-38	3/8	#8 AWG	#8 FLEX		0.406	0.8750	0.3740	0.5000	0.5620	1.5700	RED	I-21	ILD-21	(
<input type="checkbox"/>	CSWS-8-12	1/2	#8 AWG	#8 FLEX		0.562	1.2500	0.3740	0.5000	0.5620	1.9450	RED	I-21	ILD-21	(
<input type="checkbox"/>	CSWS-6-10	10	#6 AWG	#6 FLEX		0.219	0.5620	0.4110	0.5000	0.5620	1.2570	BLUE	I-24	ILD-24	(
<input type="checkbox"/>	CSWS-6-14	1/4	#6 AWG	#6 FLEX		0.281	0.6800	0.4110	0.5000	0.5620	1.3750	BLUE	I-24	ILD-24	(
<input type="checkbox"/>	CSWS-6-516	5/16	#6 AWG	#6 FLEX		0.343	0.8750	0.4110	0.5000	0.5620	1.5700	BLUE	I-24	ILD-24	(
<input type="checkbox"/>	CSWS-6-38	3/8	#6 AWG	#6 FLEX		0.406	0.8750	0.4110	0.5000	0.5620	1.5700	BLUE	I-24	ILD-24	(
<input type="checkbox"/>	CSWS-6-12	1/2	#6 AWG	#6 FLEX		0.562	1.2500	0.4110	0.5000	0.5620	1.9450	BLUE	I-24	ILD-24	(
<input type="checkbox"/>	CSWS-4-10	10	#4 AWG		4-6 AWG	0.219	0.5620	0.4860	0.5000	0.5620	1.2960	GRAY	I-29	ILD-29	(
<input type="checkbox"/>	CSWS-4-14	1/4	#4 AWG		4-6 AWG	0.281	0.6800	0.4860	0.5000	0.5620	1.4140	GRAY	I-29	ILD-29	(
<input type="checkbox"/>	CSWS-4-516	5/16	#4 AWG		4-6 AWG	0.343	0.8750	0.4860	0.5000	0.5620	1.6090	GRAY	I-29	ILD-29	(
<input type="checkbox"/>	CSWS-4-38	3/8	#4 AWG		4-6 AWG	0.406	0.8750	0.4860	0.5000	0.5620	1.6090	GRAY	I-29	ILD-29	(
<input type="checkbox"/>	CSWS-4-12	1/2	#4 AWG		4-6 AWG	0.562	1.2500	0.4860	0.5000	0.5620	1.9840	GRAY	I-29	ILD-29	(
<input type="checkbox"/>	CSWS-3-10	10	#3 AWG	#4 FLEX	3-6 AWG	0.219	0.5620	0.5320	0.6250	0.6870	1.4420	WHITE	I-29	ILD-29	(
<input type="checkbox"/>	CSWS-3-14	1/4	#3 AWG	#4 FLEX	3-6 AWG	0.281	0.6800	0.5320	0.6250	0.6870	1.5600	WHITE	I-29	ILD-29	(
<input type="checkbox"/>	CSWS-3-516	5/16	#3 AWG	#4 FLEX	3-6 AWG	0.343	0.8750	0.5320	0.6250	0.6870	1.7550	WHITE	I-29	ILD-29	(
<input type="checkbox"/>	CSWS-3-38	3/8	#3 AWG	#4 FLEX	3-6 AWG	0.406	0.8750	0.5320	0.6250	0.6870	1.7550	WHITE	I-29	ILD-29	(
<input type="checkbox"/>	CSWS-3-12	1/2	#3 AWG	#4 FLEX	3-6 AWG	0.562	1.2500	0.5320	0.6250	0.6870	2.1300	WHITE	I-29	ILD-29	(

[Contact Us](#) [Privacy Policy](#)

©1991-2013 [CDI Technology](#) All Rights Reserved

ILSCO
4730 MADISON ROAD
CINCINNATI, OH 45227
513-533-6200
800-776-9775