

TYPE

LDA

LDB

Features

- Modular design
- Easy to assemble
- UL listed 90° C 600 Volts and is CSA Certified
- Electro-tin plated 6061-T6 aluminum alloy
- Clear cover
- Multiple conductor capability

Benefits

- Simplifies stocking. Combines any number of blocks with multiple conductor ranges into the specific configuration required for the job.
- Unique locking feature allows individual blocks to be combined quickly without special tools
- Ensures reliability
- Suitable for use with both copper and aluminum conductors in any combination
- Permits visual inspection
- Individual blocks supplied in a variety of configurations with one or two main cable ports and four, six, or twelve taps. All are range taking.



Fig. 1




Fig. 2

Catalog Number	Figure Number	Connector		Primary		Secondary			Ampere	
		Primary	Secondary	Wire Range	Openings Per Pole	Hex Size	Wire Range	Openings Per Pole	Hex Size	Rating Per Pole
LDB-112-350	1			350kcmil-6	1	3/8	4-14	12	Slot	310
LDA-112-350	2			350kcmil-6	1	3/8	4-14	12	Slot	310
LDB-112A-350	1			350kcmil-6	1	3/8	4-14	12	Slot	310
LDA-112A-350	2			350kcmil-6	1	3/8	4-14	12	Slot	310
LDB-16-350	1			350kcmil-6	1	3/8	2/0-14	6	3/16	310
LDA-16-350	2			350kcmil-6	1	3/8	2/0-14	6	3/16	310
LDB-16-500	1			500kcmil-4	1	3/8	2/0-14	6	3/16	380
LDA-16-500	2			500kcmil-4	1	3/8	2/0-14	6	3/16	380
LDB-26-350	1			350kcmil-6	2	3/8	2/0-14	6	3/16	620
LDA-26-350	2			350kcmil-6	2	3/8	2/0-14	6	3/16	620
LDB-212-4/0	1			4/0-6	2	1/4	4-14	12	Slot	460
LDA-212-4/0	2			4/0-6	2	1/4	4-14	12	Slot	460
LDB-212-500	1			500kcmil-4	2	3/8	4-14	12	Slot	760
LDA-212-500	2			500kcmil-4	2	3/8	4-14	12	Slot	760
LDB-26-500	1			500kcmil-4	2	3/8	2/0-14	6	3/16	760
LDA-26-500	2			500kcmil-4	2	3/8	2/0-14	6	3/16	760
LDB-24-500	1			500kcmil-4	2	3/8	4/0-6	4	5/16	760
LDA-24-500	2			500kcmil-4	2	3/8	4/0-6	4	5/16	760
LDB-11-500	1			500kcmil-4	1	3/8	500kcmil-4	1	3/8	380
LDA-11-500	2			500kcmil-4	1	3/8	500kcmil-4	1	3/8	380
LDB-22-350	1			350kcmil-6	2	3/8	350kcmil-6	2	3/8	620
LDA-22-350	2			350kcmil-6	2	3/8	350kcmil-6	2	3/8	620
LDB-22-500	1			500kcmil-4	2	3/8	500kcmil-4	2	3/8	760
LDA-22-500	2			500kcmil-4	2	3/8	500kcmil-4	2	3/8	760

Side Panel can be ordered separately Cat. No. LDS-1

Tested to UL 1059, UL File E112158



Dimensions

A	B	C	D=Dia.	E	F	G	H	J = Cover	K	L	M	N
3	5-1/2	3-7/16	.28 Slot	1-1/2	5/16	4-7/8	1/4	1/2	4.75	2.69	.38	1.50