

## TYPE PBT

### Features

- Broad wire range: 750kcmil-14
- UL Listed for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

### Benefits

- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming





Fig. 1



Fig. 2



Catalog Number	Figure No.	No. Of Ports	Wire Range	Dimensions			Hex Size
				L	W	H	
PBT-1/0	1	-	1/0-14	3.25	0.94	1.63	3/16
PBT-250	1	-	250kcmil-6	3.96	1.19	2.17	5/16
PBT-350	1	-	350kcmil-6	4.43	1.31	2.62	5/16
PBT-500	1	-	500kcmil-4	5.38	1.44	3.03	3/8
PBT-750	1	-	750kcmil-250kcmil	7.25	1.75	3.16	1/2
PBTO-4	2	2	4-14	1.24	1.25	1.42	1/8
PBTO-1/0	2	2	1/0-14	1.63	1.63	1.63	3/16
PBTO-3/0	2	2	3/0-6	1.89	1.68	1.86	3/16

Replacement caps & plugs available. Consult Factory

Tested to UL 486A-486B, UL File E6207