


TYPE PBTD

Features

- Broad wire range: 750kcmil-14
- UL Listed for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

Benefits

- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming



D

Catalog Number	No. Of Ports	Wire Range	Dimensions			Hex Size
			L	W	H	
PBTD-10-3/0	10	3/0-6	8.01	1.68	1.86	3/16
PBTD-11-3/0	11	3/0-6	8.77	1.68	1.86	3/16
PBTD-12-3/0	12	3/0-6	9.54	1.68	1.86	3/16
PBTD-13-3/0	13	3/0-6	10.30	1.68	1.86	3/16
PBTD-14-3/0	14	3/0-6	11.07	1.68	1.86	3/16
PBTD-2-250	2	250kcmil-6	2.17	2.13	2.17	5/16
PBTD-3-250	3	250kcmil-6	3.07	2.13	2.17	5/16
PBTD-4-250	4	250kcmil-6	3.96	2.13	2.17	5/16
PBTD-5-250	5	250kcmil-6	4.85	2.13	2.17	5/16
PBTD-6-250	6	250kcmil-6	5.75	2.13	2.17	5/16
PBTD-7-250	7	250kcmil-6	6.64	2.13	2.17	5/16
PBTD-8-250	8	250kcmil-6	7.53	2.13	2.17	5/16
PBTD-9-250	9	250kcmil-6	8.42	2.13	2.17	5/16
PBTD-10-250	10	250kcmil-6	9.32	2.13	2.17	5/16
PBTD-11-250	11	250kcmil-6	10.21	2.13	2.17	5/16
PBTD-12-250	12	250kcmil-6	11.10	2.13	2.17	5/16
PBTD-13-250	13	250kcmil-6	12.00	2.13	2.17	5/16
PBTD-14-250	14	250kcmil-6	12.89	2.13	2.17	5/16
PBTD-2-350	2	350kcmil-6	2.51	2.25	2.62	5/16
PBTD-3-350	3	350kcmil-6	3.56	2.25	2.62	5/16
PBTD-4-350	4	350kcmil-6	4.61	2.25	2.62	5/16
PBTD-5-350	5	350kcmil-6	5.67	2.25	2.62	5/16
PBTD-6-350	6	350kcmil-6	6.71	2.25	2.62	5/16
PBTD-7-350	7	350kcmil-6	7.76	2.25	2.62	5/16
PBTD-8-350	8	350kcmil-6	8.81	2.25	2.62	5/16
PBTD-9-350	9	350kcmil-6	9.86	2.25	2.62	5/16
PBTD-10-350	10	350kcmil-6	10.91	2.25	2.62	5/16
PBTD-11-350	11	350kcmil-6	11.96	2.25	2.62	5/16
PBTD-12-350	12	350kcmil-6	13.01	2.25	2.62	5/16
PBTD-13-350	13	350kcmil-6	14.06	2.25	2.62	5/16
PBTD-14-350	14	350kcmil-6	15.11	2.25	2.62	5/16
PBTD-2-500	2	500kcmil-4	2.97	2.63	3.04	3/8
PBTD-3-500	3	500kcmil-4	4.12	2.63	3.04	3/8
PBTD-4-500	4	500kcmil-4	5.28	2.63	3.04	3/8

Replacement caps & plugs available. Consult Factory Tested to UL 486A-486B, UL File E6207