


**TYPE
PBTD**
Features

- Broad wire range: 750kcmil-14
- UL Listed for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

Benefits

- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming


D

Catalog Number	No. Of Ports	Wire Range	Dimensions			Hex Size
			L	W	H	
PBTD-5-500	5	500kcmil-4	6.44	2.63	3.04	3/8
PBTD-6-500	6	500kcmil-4	7.59	2.63	3.04	3/8
PBTD-7-500	7	500kcmil-4	8.75	2.63	3.04	3/8
PBTD-8-500	8	500kcmil-4	9.90	2.63	3.04	3/8
PBTD-9-500	9	500kcmil-4	11.06	2.63	3.04	3/8
PBTD-10-500	10	500kcmil-4	12.22	2.63	3.04	3/8
PBTD-11-500	11	500kcmil-4	13.37	2.63	3.04	3/8
PBTD-12-500	12	500kcmil-4	14.53	2.63	3.04	3/8
PBTD-13-500	13	500kcmil-4	15.68	2.63	3.04	3/8
PBTD-14-500	14	500kcmil-4	16.84	2.63	3.04	3/8
PBTD-2-750	2	750kcmil-250kcmil	3.47	3.25	3.31	1/2
PBTD-3-750	3	750kcmil-250kcmil	4.89	3.25	3.31	1/2
PBTD-4-750	4	750kcmil-250kcmil	6.32	3.25	3.31	1/2
PBTD-5-750	5	750kcmil-250kcmil	7.74	3.25	3.31	1/2
PBTD-6-750	6	750kcmil-250kcmil	9.16	3.25	3.31	1/2
PBTD-7-750	7	750kcmil-250kcmil	10.58	3.25	3.31	1/2
PBTD-8-750	8	750kcmil-250kcmil	12.00	3.25	3.31	1/2
PBTD-9-750	9	750kcmil-250kcmil	13.43	3.25	3.31	1/2
PBTD-10-750	10	750kcmil-250kcmil	14.85	3.25	3.31	1/2
PBTD-11-750	11	750kcmil-250kcmil	16.27	3.25	3.31	1/2
PBTD-12-750	12	750kcmil-250kcmil	17.69	3.25	3.31	1/2
PBTD-13-750	13	750kcmil-250kcmil	19.11	3.25	3.31	1/2
PBTD-14-750	14	750kcmil-250kcmil	20.54	3.25	3.31	1/2

Replacement caps & plugs available. Consult Factory

Tested to UL 486A-486B, UL File E6207