

ILSCO Aluminum Multi-Tap Connectors - Dual Rated



TYPE PED-Z

Features

- Available in two, four, six, or eight conductor configurations in four wire ranges
- Manufactured from high strength 6061-T6 aluminum alloy
- UL Listed
- Compact size
- Rated for 600 volts, 90° C

Benefits

- Provides multiple conductor installation for a wide range of conductors
- Suitable for use with either copper or aluminum conductors
- Ensures reliability
- Suitable for pedestal applications
- Ensures reliability

C



Catalog Number	Connector Design	Number Of Ports	Wire Range	Dimensions			Hex Size
				L	W	H	
PED-2-2/0-Z		2	2/0-14	2.09	.56	.73	3/16
PED-4-2/0-Z		4	2/0-14	3.78	.56	.73	3/16
PED-6-2/0-Z		6	2/0-14	5.46	.56	.73	3/16
PED-8-2/0-Z		8	2/0-14	7.15	.56	.73	3/16
PED-2-4/0-Z		2	4/0-6	2.23	.75	1.00	5/16
PED-4-4/0-Z		4	4/0-6	4.09	.75	1.00	5/16
PED-6-4/0-Z		6	4/0-6	5.95	.75	1.00	5/16
PED-8-4/0-Z		8	4/0-6	7.81	.75	1.00	5/16
PED-2-350-Z		2	350kcmil-6	2.72	1.00	1.25	5/16
PED-4-350-Z		4	350kcmil-6	5.03	1.00	1.25	5/16
PED-6-350-Z		6	350kcmil-6	7.34	1.00	1.25	5/16
PED-8-350-Z		8	350kcmil-6	9.65	1.00	1.25	5/16
PED-2-600-Z		2	600kcmil-4	2.62	1.38	1.75	1/2
PED-4-600-Z		4	600kcmil-4	5.36	1.38	1.75	1/2
PED-6-600-Z		6	600kcmil-4	8.10	1.38	1.75	1/2
PED-8-600-Z		8	600kcmil-4	10.84	1.38	1.75	1/2

Covers not available.

DE-OX Inhibitor is recommended for all aluminum terminations.

