



Aluminum Splicer/Reducer - Dual Rated



TYPE SPA



Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro-tin plated
- Chamfered wire entry
- UL Listed and CSA Certified for 600 volts
- Rounded bottoms
- Large screw diameters
- Wire stop in center

Benefits

- Suitable for use with either copper or aluminum conductors
- Provides low contact resistance
- Provides ease of installation
- Ensures reliability for copper or aluminum conductors
- Facilitates taping
- Ensures all wire strands are held securely
- Prevents dissimilar metals coming into contact

Rated for 600 Volts



Catalog Number	Wire Range	Dimensions			Number of Screws	Screw Diameter	Hex Size	Temperature Rating
		F	H	T				
SPA-2	2-14	1-3/16	29/64	9/16	2	3/8	Slot	90° C
SPA-0	1/0-14	1-29/32	5/8	11/16	2	7/16	Slot	90° C
SPA-4/0	4/0-6	2-5/16	1	1-3/32	2	9/16	5/16	90° C
SPA-250	250MCM-6	4-3/32	1	1-3/32	4	5/8	5/16	90° C
SPA-350	350MCM-6	4-11/32	1	1-3/32	4	11/16	5/16	90° C
SPA-500	500MCM-3/0	4-25/32	1-1/4	1-3/8	4	13/16	3/8	90° C
SPA-750	750MCM-250MCM	6-1/16	1-7/16	1-5/8	4	15/16	1/2	90° C
SPA-1000	1000MCM-500MCM	8-11/16	1-23/32	1-7/8	6	1-1/8	9/16	90° C

DE-OX Inhibitor is recommended for all aluminum terminations.