

NEW



Model #	Input Voltage
FM1D14-12U	12 VDC
FM1D14-24U	24 VAC/VDC, 50/60Hz
FM1D14-AV-U	120-277 VAC, 50/60Hz

NOTE: Clear dust cover order #DC-FME

FM1D14 Series One-Circuit Panel Mount



- 24-Hour or 7-Day applications
- 14 setpoint programs
- Simple-to-use programming
- Manual override with status indication
- Rechargeable battery backup with industry-leading 2500-Hour carryover
- 5 preset adjustable block programs

Ratings:

Power Consumption: 1.4 W
Switch Type: SPDT relay
N.O. Contact:
 15A, 277 VAC, General Use
 10 FLA, 60 LRA, 250 VAC
 ½ HP, 120 VAC, 1 HP, 250 VAC
 1000 W, 120 VAC, Tungsten
 8 A, 277 VAC, STD Ballast
 B300 Pilot Duty
 4.9 A, 120 VAC, Electronic Ballast

N.C. Contact:

15 A, 277 VAC, General Use
 10 FLA, 60 LRA, 250 VAC
 ½ HP, 120/240 VAC
 12 A, 24 VDC, Resistive
 8 A, 120 VAC, STD Ballast
Dimensions:
 2.36" x 2.36" (60 mm x 60 mm)
Wiring Connections:
 ¼" quick connect terminals
Operating Temperature:
 -40°F to 131°F (-40°C to 55°C)
 (limited display function at -13°F)
Warranty: 1-year limited



Model #	Input Voltage
FM2D50-24	24 VAC/VDC, 50/60 Hz
FM2D50-120	120 VAC, 50/60 Hz
FM2D50-240	240 VAC, 50/60 Hz

FM2D50 Series Two-Circuit Surface and Flush Mount



- 24-Hour or 7-Day applications
- Screw terminals for #10 to #24 AWG
- Clear dust cover
- 50 setpoint programs
- Free weekday block formation
- Selectable languages: English, German, French, Italian, Spanish, Portuguese, and Dutch
- Auto Daylight Saving Time adjustment
- Easy-to-follow menu driven programming
- Manual override with load status indication
- Battery backup with 3-year carryover
- Each circuit operates independently or combined
- Heavy-duty relay contacts for switching low or line voltage loads

Ratings:

Power Consumption: 4 VA
Switch Type: 2x SPDT Relay
N.O. and N.C. Contact:
 16 A, 277 VAC Resistive
 ½ HP, 120 VAC, 1 HP, 240 VAC
 12 A, Ballast 120 VAC, 8A, Ballast 240 VAC
 720 VA, 240 VAC Pilot Duty 360 VA, 120 VAC Pilot Duty
 600 W, Tungsten, 120 VAC 100 W, Tungsten 240 VAC
Wiring Connection: Screw terminals for #10 to #24 AWG
Warranty: 1 year



For DIN rail mounting, order MB-DIN (DIN Rail Mounting Base)
 See Accessories on Page 153