



Actual

Catalog Number: ADR25-44
Product ID: 7TAH006600R0211
UPC Number: 78378661015
Status: Active

Type ADR-ALCUL Four-Conductor, Four-Hole Mount for Conductor Range Max 250 kcmil, Min 6 Str.

- Easy Installation - no special tools required.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Dual-Rated Mechanical Connector
Special Features	Easy Installation - no special tools required.
Standard	UL E9809
Number Of Conductors	4
Material	Aluminum
Finish	Tin-Plated
Conductor Range (Main/Primary)	6-250
Number Of Mounting Holes	4

Packaging

Inner Quantity	3
Inner Dimensions (inches)	5x5x2.25
Outer Quantity	30
Outer Dimensions (inches)	13.5x10.5x7
Weight Uom	70 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com