

Swimming Pool & Spa Controls and Control Centers

Model T21004R



These Control Centers feature an all-weather enclosure and contain a 4 circuit breaker base, an equipment grounding bar and a mechanical or electronic timer mechanism. The circuit breaker base accepts interchangeable type breakers made by a number of different manufacturers. In addition, the enclosure has provision for installing additional switches or GFCI receptacles on the side and inside.

APPLICATIONS

- ▲ Pumps
- ▲ Ventilating Systems
- ▲ Air Conditioners
- ▲ Lights
- ▲ Signs
- ▲ Heaters

60 AMP CONTROL CENTERS

Model Number	Description/Mechanism	Switch	Clock Supply Volts 60 Hz.
T20001R	T101M - Mechanical	SPST	120
T21004R	T104M - Mechanical	DPST	208 - 277

For additional trippers (1 "ON" 1 "OFF" per pack), order No. 156T1978A.

SPECIFICATIONS

CASE - 16" (40.64 cm) high x 8.5" (21.59 cm) wide x 4" (10.2 cm) deep. 0.048" steel with electrostatically applied light beige finish.

KNOCKOUTS - Five combination 1/2"-3/4" and three 3/4" - 1" on the bottom, one combination 1/2"-3/4" on the left side, one 3/4"-1" on the back and one combination 1-3/4" x 2-3/4" knockout on the right side for mounting switches or GFCI.

PANEL RATING - 60 Amp. 120/240 Volt or 120/208 Volt; Single Phase-60 Hz.

TIME SWITCH RATING - Mechanical: 40 Amp. resistive each pole 120-240 V.A.C., 40 Amp. tungsten, inductive or 1000 VA pilot duty each pole 120-240 V.A.C. 2 H.P. (24 FLA) - 120 V.A.C.; 5 H.P.(28 FLA) - 240 V.A.C.

SHIPPING WEIGHT - 14 lbs. (6-3 kg)

AGENCY APPROVAL - UL, CSA

Model PF1222TB

Model PF1202T



These heavy-duty Freeze Protection Controls are designed specifically for pools requiring one or two time switches as well as freeze protection. In addition, it has a provision to install switches inside or GFCI receptacle on the side of enclosure.

APPLICATIONS

- ▲ Filter Pumps
- ▲ Fountains
- ▲ Filter Pump-Booster Pump Combinations
- ▲ Pool-Spa Combinations

MULTI CIRCUIT FREEZE PROTECTION CONTROLS

Model Number	Description	Electrical Input	Rating H.P.	Shipping Weight
PF1112T	For pools requiring one time switch	240V	3	8.0 lbs.
PF1202T	For pools with cleaner, requiring two time switches	240V	3	10.0 lbs.
PF1222TB	Same as a PF1202T with 4/8 breaker base and heater protection	240V	3	17.0 lbs.

For additional trippers (2 "ON" 2 "OFF" per pack), order No. 156TN10398A.

SPECIFICATIONS

CASE - Model PF1112T and PF1202T same as Model T10404R on page 55

AGENCY APPROVAL - UL

CASE - Model PF1222TB, 16-1/2" (41.9cm) high x 10-7/8" (27.6 cm) wide x 4/1/4" (10.8 cm) deep, 0.048" steel with electrostatically applied beige finish.

ELECTRICAL RATING - See table.

SHIPPING WEIGHT - See table.

THERMOSTAT RANGE - 45°F - 32°F with 5 degrees differential.

AGENCY APPROVAL - UL, CSA