

Decorator Spring Wound Timers



FD30MAC
Ivory



FD30MAC
Almond



FD60MWC
White



UL917
E10694



UL917
E10694



C22.2-177
LR3730
UL917



2.5 lbs
1.1 kg



-40°F
(-40°C)
to
155°F
(68°C)

FD Decorator Series Auto-Off Timers

Features:

- Energy saving timers use no electricity to operate
- Designed to replace any standard wall switch, single or multi-gang
- Automatically limits ON time of fans, lights, motors, heaters and other energy-consuming loads
- Time limits of 5, 15, 30 and 60 minutes and 2, 4, 6, and 12 hours available
- "Hold feature" allows the user to override the automatic shut-off function for extended use of the load as required
- Supplied with a molded white, ivory, or almond time dial plate designed to fit either toggle or decorator style switch plates
- Single or multi-gang with no field modifications required to fit either style switch plate
- Time saving "up front" terminal connection with teeter type terminals
- Easy "press-on" knob design ensures quick and easy installation

Applications:

- Indoor Lighting
- Outdoor Lighting
- Lighting Overrides
- Exhaust Fans
- Whole House Fans
- Ventilating Fans
- Tennis Court Lighting
- Pumps
- Air Conditioners
- Steam Rooms
- Bathroom Fans
- Whirlpools
- Porch Lights
- Broom Closets
- Carriage Lights
- Television Sets
- Self Storage Units
- Engine Block Heaters
- Process Controls

Specifications:

Switch Rating:

Resistive: 20 Amp, 125 VAC, 50/60 Hz; 10 Amp, 250 VAC, 50/60 Hz; 10 Amp, 277 VAC, 50/60 Hz

Tungsten: 7 Amp, 125 VAC

Motor: 1 HP, 125 VAC, 50/60 Hz; 2 HP, 250 VAC, 50/60Hz

Caution: Do not use for sunlamps, sauna, etc...

Style: Decorator Styling — Can be used with decorator or toggle type switch plates (Not included)

Time Cycle	Switch	Hold	IVORY	WHITE	ALMOND
5 Min	SPST	No	FD5M	FD5MW	—
15 Min	SPST	No	FD15MC	FD15MWC	FD15MAC
15 Min	SPST	Yes	FD15MH	FD15MHW	—
30 Min	SPST	No	FD30MC	FD30MWC	FD30MAC
30 Min	SPST	Yes	FD30MH	FD30MWH	—
60 Min	SPST	No	FD60MC	FD60MWC	FD60MAC
60 Min	SPST	Yes	FD60MH	FD60MHW	—
2 Hr	SPST	No	FD2H	FD2HW	—
4 Hr	SPST	No	FD4H	FD4HW	—
6 Hr	SPST	No	FD6H	FD6HW	—
6 Hr	SPST	Yes	FD6HH	FD6HHW	—
12 Hr	SPST	No	FD12HC	FD12HWC	—
12 Hr	SPST	Yes	FD12HH	FD12HHW	—
2 Hr	SPDT	No	FD32H	FD32HW	—
4 Hr	SPDT	No	FD34H	FD34HW	—
6 Hr	SPDT	No	FD36H	—	—
12 Hr	SPDT	No	—	FD312HW	—
15 Min	DPST	No	FD415M	—	—
30 Min	DPST	No	FD430M	FD430MW	—
60 Min	DPST	No	FD460M	FD460MW	—
6 Hr	DPST	No	FD46H	FD46HW	—

Note: For Replacement Knob information see page 159.