

E1020

Heavy-Duty In-Wall Time Switch



- Includes two ON and OFF Trippers
- Dial accomodates a total of 12 ON and 12 OFF events
- Turns ON/OFF heavy-duty loads for energy savings, security, and convenience
- Mounts to any standard junction box
- Neutral wire required
- Manual override

Model #	Switch	Color
H. E1020	SPST	Stonedust White Housing

Additional trippers (156EB1945A) sold separately page 153

Ratings:

Switch: SPST

Switch Rating: 125 VAC, 60 Hz., 1500 W Tungsten, 12 FLA, 15 A Resistive

Max. Wattage: 1800 W

Timing Cycle: Minimum ON time ½ hour, Maximum ON time 22 ½ hours

Minimum time between any two ON trippers (or 2 OFF trippers) is 2 hours

Dimensions: 4 ¼" (10.8 cm) H x 3 ¼" (9.5 cm) W x 1 ⅝" (3.5 cm) D

Warranty: Limited 1 year



H.

E1010

Heavy-Duty In-Wall Time Switch



- Permanently attached ON/OFF tripper permits single ON/OFF control every 24 hours
- 24-Hour dial divided in 30 minute increments
- Turns ON/OFF heavy-duty loads for energy savings, security, and convenience
- Mounts to any standard junction box
- Neutral wire required
- Manual override

Model #	Switch	Color
J. E1010	SPST	Stonedust White Housing

Ratings:

Switch: SPST

Switch Rating: 125 VAC, 60 Hz., 1500 W Tungsten, 12 FLA, 15 A Resistive

Max. Wattage: 1800 W

Timing Cycle: Minimum ON time ½ hour, Maximum ON time 22 ½ hours

Only 1 ON and 1 OFF Tripper

Dimensions: 4 ¼" (10.8 cm) H x 3 ¼" (9.5 cm) W x 1 ⅝" (3.5 cm) D

Warranty: Limited 1 year



J.