

Nonmetallic Threaded Strain Relief Connector c/w "O" Ring, Locknut & 6 Grommets









Size (in)	Part Number	Product Code
1/2	TSRC10	077754
3/4	TSRC15	077756

Strain Relief Connectors c/w 6 Grommets



Size (in)	Part Number	Product Code
3/4	SRC15	077985

Strain Relief Connectors Grommet Dimensions

Grommet	From	To
	W = .195" L = .450"	W = .285" L = .530"
	W = .220" L = .516"	W = .291" L = .565"
	Ø = .240"	Ø = .300"
	Ø = .290"	Ø = .385"
	Ø = .405"	Ø = .500"
	Ø = .525"	Ø = .625"

Note: All grommets are supplied with TSRC10, TSRC15 and SRC15.

F Series - Single Gang Plates



DRC15/10 TSC15/10 20RC15/10 20-3RC15/10 30-3RC15/10 BRC15/10 GASK15/10


Description	Part Number	Product Code
Duplex Receptacle	DRC15/10	077617
Toggle Switch	TSC15/10	077616
Single Receptacle	20RC15/10	077618
Single Receptacle	20-3RC15/10	077619
Single Receptacle	30RC15/10	077620
Blank c/w Gasket	BRC15/10	077611
PVC Gasket	GASK15/10	077621

F Series - Double Gang Plates



Description	Part Number	Product Code
Blank Cover c/w Gasket	BRC20-2	077614
Double Switch	TSC20-2	077738
Double Duplex Receptacle	DRC20-2	077740
Combo Switch Duplex Rec.	TSDC20-2	077739
PVC Gasket	GASK20-2	077743

F Series - Triple Gang Plates



Description	Part Number	Product Code
Triple Receptacle	DRC20-3	077747
Combo Switch Receptacle	DSDR20-3	077745
Triple Switch	TSC20-3	077744
Combo Switch Receptacle	TSDC20-3	077746
Blank Cover c/w Gasket	BRC20-3	077748
PVC Gasket	GASK20-3	077749

