

# Line Voltage Halogen



Provides economical halogen lighting by utilizing 120-volt halogen lamps which do not require a transformer.

### Performance Features

- Economical 120-volt, 25-watt halogen lamps provide a somewhat warmer tone than low voltage halogen lamps
- 2,000 hour lamp life
- Dimmable with standard incandescent wall box dimmers or integral high/low/off rocker switch

### Construction Features

- Compact 3"D x 1-5/16"H extruded aluminum profile
- Internal specular reflector maximizes light output while managing fixture/cabinet contact temperature
- Slide-in frosted tempered glass lens
- Designer White finish

### Installation Features

- Modular design is optimized for portable plug-in installations and plug-together connection of multiple fixtures
- May be permanently direct wired using optional Direct Wire Module
- Captive external mounting screws



### Fixtures

#### UH106-WH – 6" 1-Lamp Line Voltage Halogen

Supplied with field-shortenable 6' cord and plug, joiner connector, (1) G8 120V 25W bi-pin halogen lamp, and mounting hardware.

6-1/8" L x 3"D x 1-5/16" H  
(Add 2" to length for side entry of power cord.)

**Finish:** Designer White



#### UH212-WH – 12" 2-Lamp Line Voltage Halogen

Supplied with field-shortenable 6' cord and plug, joiner connector, (2) G8 120V 25W bi-pin halogen lamps, and mounting hardware.

12-1/8" L x 3"D x 1-5/16" H  
(Add 2" to length for side entry of power cord.)

**Finish:** Designer White



#### UH318-WH – 18" 3-Lamp Line Voltage Halogen

Supplied with field-shortenable 6' cord and plug, joiner connector, (3) G8 120V 25W bi-pin halogen lamps, and mounting hardware.

17-3/4" L x 3"D x 1-5/16" H  
(Add 2" to length for side entry of power cord.)

**Finish:** Designer White



### Accessories

#### DWM1-WH – Direct Wire Module

Required for permanent wiring of Line Voltage Halogen fixtures. Includes wiring enclosure and 36" field-shortenable jumper cord to bring power to right or left side of the fixture.

3" L x 3" D x 1" H

**Finish:** Designer White



#### JC2-8 (8"), JC2-17 (17"), JC2-26 (26") – Jumper Cords

2-wire Jumper Cord to electrically join fixtures when spaced apart, turning corners, or spanning cabinet frames.

**Finish:** Designer White



#### T925 – Replacement Lamp

G8 120V 25W Bi-pin halogen lamp

### Line Voltage Halogen Installation Options



Portable Installation



Direct Wire Installation



Joining Multiple Fixtures



Joining Multiple Fixtures

