

KICHLER



Direct Wire Low V Xenon - Direct-Wire 4Lt Xenon 12v/18w

10584SS

Direct-Wire 4Lt Xenon 12v/18w

Dia./Width: 5.0 IN
Body Height: 1.0 IN
Length: 30.0 IN


Available Finishes: White,
Stainless Steel, Bronze

Featuring a Stainless Steel finish which employs a 4-light design that uses 18-watt (max.) Xenon bulbs (included), this Series II Kichler Cabinet Light is perfect for almost any application. It includes an on-off switch, has a slim 1" profile, making it easy to conceal under your cabinet, and a single BX connector is included with the package.

Technical Information

Type	Cabinet Lights	Primary Bulb Count	4
Style	Utility	Primary Max Watt	18W
Finish Group	Silver	Primary Lamp Type	T5
Body Height	1 IN	Switching	Hi-Low-Off, Rocker
Length	30 IN	UL CSA Listed	Yes
Width	5 IN	Diffuser Description	Frosted
Bulb Included	Included	Body Material	Stainless Steel

Related Products



Cable Connector Single Bx

Finish: Silver Various
 Dia./Width: 1.18
 Body Height: 0.874



Cable Connector Duplex Bx

Finish: Silver Various
 Dia./Width: 1.76
 Body Height: 0.851