

# KICHLER



## No Family Association - In-Ground 1-Lt 12V 15088BK

Landscape Accent

**Dia./Width: 5.5 IN**  
**Body Height: 8.0 IN**

### Available Finishes:

Black Material (Not Painted)

36-WATT PAR 36 WELL LIGHT - Versatile design with reversible support sleeve to accommodate uplighting when flush mounted or angled lighting effects when semi-recessed. Stainless steel yolk design holds lamp securely at desired angle.

### Technical Information

Type	12v Accent / Spotlight	Bulb Included	Not Included
Style	Eclectic	Primary Bulb Count	1
Finish Group	Black	Primary Max Watt	36W
Room	Outdoor Lighting	Voltage	12V
Body Height	8 IN	UL CSA Listed	Yes
Width	5.5 IN	Body Material	Stainless Steel & Polypropylene
Extra Lead	42 IN		

### Related Products



**Path & Spread 1-Lt 12V**

Finish: Textured Black  
Dia./Width: 8.5  
Body Height: 21.0



**Underwater 1-Lt 12V**

Finish: Black Material (Not Painted)  
Dia./Width: 4.0  
Body Height: 5.0



**Accessory Cable 10ga 250 ft**

Finish: Black Material (Not Painted)  
Dia./Width: 0.0  
Body Height: 0.0



**Accessory Photocell Plug-In**

Finish: Black Material (Not Painted)  
Dia./Width: 0.0  
Body Height: 3.0