



**No Family Association - Path & Spread 1-Lt 12V**  
15310AZT

Path & spread light fixture 12V

**Dia./Width: 8.25 IN**  
**Body Height: 21.0 IN**

**Available Finishes:**  
Textured Architectural  
Bronze, Beach, Textured  
Black

DOME PATH LIGHT - A wider path and spread light that is unobtrusive in the landscape. Available in Textured Architectured Bronze. or sandy-colored Beach finish coordinating with lighter-colored pathways and home exterior finishes.

**Technical Information**

Type	12v Path and Spread	Width	8.25 IN
Style	Contemporary / Modern	Extra Lead	24 IN
Finish Group	Hand Painted	Bulb Included	Included
Room	Outdoor Lighting	Voltage	12V
Weight	3 LBS	UL CSA Listed	Yes
Body Height	21 IN	Body Material	Aluminum

**Related Products**



**Accent 1-Lt 12V**  
Finish: Textured Architectural Bronze  
Dia./Width: 2.5  
Body Height: 6.0



**Accent 1-Lt 12V**  
Finish: Textured Architectural Bronze  
Dia./Width: 2.5  
Body Height: 6.0



**Step 1-Lt 12V**  
Finish: Textured Architectural Bronze  
Dia./Width: 5.0  
Body Height: 3.5



**Step 2-Lt 12V**  
Finish: Textured Arc  
Dia./Width: 9.5  
Body Height: 4.0