

KICHLER



No Family Association - Path & Spread 1-Lt 12V 15310BKT

Path & spread light fixture 12V

Dia./Width: 8.5 IN
Body Height: 21.0 IN

Available Finishes:
Textured Architectural
Bronze, Beach, Textured
Black

DOME PATH LIGHT - A wider path and spread light that is unobtrusive in the landscape. Available in Textured Architectural Bronze, or sandy-colored Beach finish coordinating with lighter-colored pathways and home exterior finishes.

Technical Information

Type	12v Path and Spread	Bulb Included	Included
Style	Contemporary / Modern	Primary Bulb Count	1
Finish Group	Black	Primary Max Watt	16.25W
Room	Outdoor Lighting	Primary Lamp Type	921
Body Height	21 IN	Voltage	12V
Width	8.5 IN	UL CSA Listed	Yes
Extra Lead	24 IN	Body Material	Aluminum

Related Products



In-Ground 1-Lt 12V

Finish: Black Material (Not Painted)
Dia./Width: 4.0
Body Height: 5.0



Accent 1-Lt 12V

Finish: Textured Black
Dia./Width: 2.5
Body Height: 6.0



Underwater 1-Lt 12V

Finish: Black Material (Not Painted)
Dia./Width: 4.0
Body Height: 5.0



Accent 1-Lt 12V

Finish: Textured Black
Dia./Width: 2.5
Body Height: 6.0