

KICHLER



No Family Association - Path & Spread 1-Lt 12V 15410AZT

Path & Spread 1-Lt 12V

Dia./Width: 8.25 IN
Body Height: 15.0 IN

Available Finishes: Beach,
Textured Architectural
Bronze

DOME PATH LIGHT - A shorter version of our popular 15310 designed for use with lower planting and smaller garden areas.

Technical Information

Type	12v Path and Spread	Bulb Included	Included
Style	Contemporary / Modern	Primary Bulb Count	1
Finish Group	Hand Painted	Primary Max Watt	16W
Room	Outdoor Lighting	Primary Lamp Type	921
Weight	3 LBS	Voltage	12V
Body Height	15 IN	UL CSA Listed	Yes
Width	8.25 IN	Body Material	Aluminum
Extra Lead	30 IN		

Related Products



Accent 1-Lt 12V

Finish: Textured Architectural Bronze
Dia./Width: 2.5
Body Height: 6.0



Accent 1-Lt 12V

Finish: Textured Architectural Bronze
Dia./Width: 2.5
Body Height: 6.0



Step 1-Lt 12V

Finish: Textured Architectural Bronze
Dia./Width: 5.0
Body Height: 3.5



Step 2-Lt 12V

Finish: Textured Arc
Dia./Width: 9.5
Body Height: 4.0