

# KICHLER



## No Family Association - Classic Path Light

15436OZ

Classic Path Light

**Dia./Width:** 6.5 IN  
**Body Height:** 27.0 IN  
**Length:** 10.75 IN

### Available Finishes:

Olde Bronze

INTAGLIO BRASS CROOK NECK PATH AND SPREAD LIGHT - A richly detailed solid and heavy crookneck path light with a brass shade that has been engraved and etched with an organic pattern.

### Technical Information

Type	12v Path and Spread	Bulb Included	Included
Style	Traditional	Primary Bulb Count	1
Finish Group	Bronze	Primary Max Watt	16.3W
Room	Outdoor Lighting	Primary Lamp Type	921X
Body Height	27 IN	Voltage	12V
Length	10.75 IN	UL CSA Listed	Yes
Width	6.5 IN	Diffuser Description	NONE
Extra Lead	26 IN	Body Material	Stamped Brass
Shade Dimensions	6.50diaX4.53 IN		

### Related Products



**In-Ground 1-Lt 12V**  
 Finish: Architectural Bronze  
 Dia./Width: 7.0  
 Body Height: 8.25



**Deck 1-Lt 12V**  
 Finish: Architectural Bronze  
 Dia./Width: 3.75  
 Body Height: 1.75



**Accessory Rock Guard**  
 Finish: Architectural Bronze  
 Dia./Width: 7.0  
 Body Height: 1.29



**Small In-Ground Well Lt.**  
 Finish: Architectural Bronze  
 Dia./Width: 7.0  
 Body Height: 8.25