



Landscape LED - 3 LED - w/ Bracket (6.9")

15745AZT

Under /Deck/Rail-Stone Cap Light 6 inch



Dia./Width: 3.0 IN
Body Height: 0.5 IN
Length: 7.0 IN

Available Finishes:

Copper, Bronzed Brass,
 Textured Architectural
 Bronze, Gray, Sand,
 Textured White

Technical Information

Type	12v LED Hardscape	Extra Lead	70 IN
Style	Eclectic	Bulb Included	Integrated
Finish Group	Hand Painted	Voltage	12
Body Height	0.5 IN	UL CSA Listed	Yes
Length	7 IN	Body Material	Aluminum
Width	3 IN		

Related Products



Accent LED 4.5W 35 deg medium
 Finish: Textured Architectural Bronze
 Dia./Width: 3.0
 Body Height: 3.5



Accent LED 8.5W 35 degree med
 Finish: Textured Architectural Bronze
 Dia./Width: 3.0
 Body Height: 3.5



Accent LED 12.4W 60 deg wide
 Finish: Textured Architectural Bronze
 Dia./Width: 3.5
 Body Height: 4.25

Accent LED 12.4W 35 deg me
 Finish: Textured Architectural Bronze
 Dia./Width: 3.5
 Body Height: 4.25