



**Landscape LED - 9 LED - w/o Bracket (18.9")**

15755AZT

Led linear Step Linear 18 inch w/o brkt



**Dia./Width:** 0.75 IN  
**Body Height:** 0.5 IN  
**Length:** 19.0 IN

**Available Finishes:**

Bronzed Brass, Copper,  
 Textured Architectural  
 Bronze, Gray, Sand,  
 Textured White

**Technical Information**

Type	12v LED Hardscape	Extra Lead	70 IN
Style	Eclectic	Bulb Included	Integrated
Finish Group	Hand Painted	Voltage	12
Body Height	0.5 IN	UL CSA Listed	Yes
Length	19 IN	Body Material	Aluminum
Width	0.75 IN		

**Related Products**



**Accent LED 4.5W 35 deg medium**  
 Finish: Textured Architectural Bronze  
 Dia./Width: 3.0  
 Body Height: 3.5



**Accent LED 8.5W 35 degree med**  
 Finish: Textured Architectural Bronze  
 Dia./Width: 3.0  
 Body Height: 3.5



**Accent LED 12.4W 60 deg wide**  
 Finish: Textured Architectural Bronze  
 Dia./Width: 3.5  
 Body Height: 4.25

**Accent LED 12.4W 35 deg me**  
 Finish: Textured Architectural Bronze  
 Dia./Width: 3.5  
 Body Height: 4.25