

KICHLER



Landscape LED - LED Deck 1-Lt 12V

15765AZT

LED Deck 1-Lt 12V

Dia./Width: 3.75 IN

Body Height: 2.5 IN

Length: 2.25 IN

Available Finishes:

Textured Architectural
Bronze, Beach, Textured
Black, White, Bronzed
Brass

LED MINI DECK LIGHT - Versatile mini size and simple styling for multiple applications with the added benefit of LED technology.

Technical Information

Type	12v LED Deck	Width	3.75 IN
Style	Transitional	Extra Lead	71 IN
Finish Group	Hand Painted	Bulb Included	Integrated
Room	Outdoor Lighting	Voltage	12
Body Height	2.5 IN	UL CSA Listed	Yes
Length	2.25 IN	Body Material	Aluminum

Related Products



Accent LED 4.5W 35 deg medium

Finish: Textured Architectural Bronze
Dia./Width: 3.0
Body Height: 3.5



Accent LED 8.5W 35 degree med

Finish: Textured Architectural Bronze
Dia./Width: 3.0
Body Height: 3.5



Accent LED 12.4W 60 deg wide

Finish: Textured Architectural Bronze
Dia./Width: 3.5
Body Height: 4.25

Accent LED 12.4W 35 deg me

Finish: Textured Architectural Bronze
Dia./Width: 3.5
Body Height: 4.25