

# KICHLER



## Ansonia - Pendant 1Lt

3349NI

Pendant 1Lt

**Dia./Width:** 15.0 IN

**Body Height:** 15.0 IN

### Available Finishes:

Brushed Nickel

Linear and futuristic in its design, the Ansonia Collection takes simple, striking shapes to form a line of fixtures that are both delicate and ultramodern. Each piece features a clean profile with an uncluttered design suitable for any home. The Ansonia Collection embraces the classic, rich Brushed Nickel finish with such zeal that it will certainly offer a fine contrast to any décor. The satin-etched glass shade offers a delicate contrast in color to provide a fine ambiance in any room. This one-light pendant measures 15" in diameter with a 15" body height and uses 150-watt G-type (max) bulbs.

### Technical Information

Type	Pendant Lighting	Extra Lead	26 IN
Style	Contemporary / Modern	Backplate Dimensions	5 DIA. IN
Finish Group	Silver	Bulb Included	Not Included
Room	Kitchen Lighting	Primary Bulb Count	1
Weight	6.8 LBS	Primary Max Watt	150W
Body Height	15 IN	Primary Lamp Type	G
Width	15 IN	UL CSA Listed	Yes
Chain Length	72 IN	Diffuser Description	SATIN ETCHED GL

### Related Products



#### Bath 3Lt

Finish: Brushed Nickel  
Dia./Width: 23.0  
Body Height: 8.75



#### Bath 2Lt

Finish: Brushed Nickel  
Dia./Width: 14.75  
Body Height: 8.75



#### Bath 4Lt

Finish: Brushed Nickel  
Dia./Width: 31.25  
Body Height: 8.75



#### Chandelier 5Lt

Finish: Brushed Nick  
Dia./Width: 22.0  
Body Height: 11.75