

KICHLER



Quinn - Wall Sconce 1Lt

42255AP

Wall Sconce 1Lt

Dia./Width: 7.5 IN

Body Height: 15.75 IN

Available Finishes:

Antique Pewter

The Quinn(TM) Collection presents traditional shapes contrasted against geometric forms that are anything but ordinary. A petite, tapered fabric shade sits atop a circular glass diffuser and oval base form that provide the smart detailing you seek on this 1 light wall sconce. 7.5 inch width. Height 16 inches. Extension 8.5 inches. Rises 10.25 inches above the center of the wall opening. Uses 1 - 60W max bulb. UL listed for damp locations.

Technical Information

Type	Wall Lights	Bulb Included	Not Included
Style	Transitional	Primary Bulb Count	1
Finish Group	Silver	Primary Max Watt	60W
Weight	2.5 LBS	Primary Lamp Type	B10
Body Height	15.75 IN	UL CSA Listed	Yes
Width	7.5 IN	Diffuser Description	SATIN ETCHED GL
Extension	8.5 IN	Shade Description	WHITE LINEN FAB
Height from Junction Box	10.25 IN	Body Material	Steel
Backplate Dimensions	11.00 X 4.75 IN		

Related Products



Pendant 3Lt

Finish: Antique Pewter
Dia./Width: 23.25
Body Height: 21.0



Chandelier 5Lt

Finish: Antique Pewter
Dia./Width: 26.75
Body Height: 22.5



Semi Flush 2Lt

Finish: Antique Pewter
Dia./Width: 17.0
Body Height: 12.5



Mini Pendant 1Lt

Finish: Antique Pew
Dia./Width: 10.0
Body Height: 12.0