

# KICHLER



## Ceiling Space - Flush Mount 1Lt

8880WH

Flush Mount 1Lt

**Dia./Width:** 10.0 IN

**Body Height:** 4.25 IN

### Available Finishes:

Brushed Nickel, White, Tannery Bronze, Olde Bronze, Polished Nickel, Black (Painted), Olde Bronze, Brushed Nickel

The simplicity of this flush mount fixture makes it an easy match for any décor. It features a 10" diameter, White finish, Satin-etched cased opal twist-on glass, and 1-light design that uses a 75-watt (max.) bulb. It is U.L. listed for damp applications.

### Technical Information

Type	Ceiling Lights	Primary Bulb Count	1
Style	Contemporary / Modern	Primary Max Watt	75W
Finish Group	White	Primary Lamp Type	A
Room	Bedroom, Hallway, Utility	UL CSA Listed	Yes
Body Height	4.25 IN	Diffuser Description	SATIN ETCHED CASED OPAL TWIST ON GLASS
Width	10 IN	Body Material	Steel
Bulb Included	Not Included		