

KICHLER



Chicago - Outdoor Wall 1Lt

9364AGZ

Outdoor Wall 1Lt

Dia./Width: 6.75 IN

Body Height: 9.5 IN

Available Finishes:

Aged Bronze

With its classic profile, this fine outdoor collection offers a fresh design that adds a sense of allure to your home. The fixture's Cast Aluminum construction is partnered with our Aged Bronze finish, making these outdoor lanterns both reliable and gorgeous accent pieces to your home. When the sun goes down, the fine, ambient light from the textured linen seedy glass panels draws additional attention to your home as it is illuminated against even the darkest of night skies. This 1-light wall lantern is easy to install, uses a 60-watt (max.) bulb, has a height of 9 ½" and is 7" wide. It is U.L. listed for wet location.

Technical Information

| | | | |
|--------------------------|---------------------------|----------------------|---------------------------|
| Type | Outdoor Lights | Extra Lead | 6 IN |
| Style | Arts and Crafts / Mission | Backplate Dimensions | 4.5" X 6" OVAL IN |
| Finish Group | Hand Painted | Bulb Included | Not Included |
| Room | Outdoor Lighting | Primary Bulb Count | 1 |
| Weight | 3 LBS | Primary Max Watt | 60W |
| Body Height | 9.5 IN | Primary Lamp Type | A19 |
| Width | 6.75 IN | UL CSA Listed | Yes |
| Extension | 7.75 IN | Diffuser Description | TEXTURED LINEN SEEDY GLAS |
| Height from Junction Box | 3 IN | Body Material | Cast Aluminum |

Related Products



52 Inch Chicago Fan

Finish: Aged Bronze

Dia./Width: 52.0

Body Height: 0.0