

## 9" Ironworker's Work Pliers

- **Custom, US-made tool steel.**
- **Hot-riveted joint** ensures smooth action and no handle wobble.
- **Induction hardened** cutting knives for long life.
- **Unique handle tempering** helps absorb the "snap" when cutting wire.
- **2000 Series** pliers available. Cuts ACSR, screws, nails and most hardened wire.
- **"Handform" handles** for full gripping and cutting power.
- **Precision-hardened plier head** for on-the-job toughness.
- **Sure-gripping** cross-hatched knurled jaws.
- **Plastic-dipped handles\*** for comfort and ease of identification.
- **\*Journeyman™ pliers available for some styles.** State-of-the-art, dual-material handles, which provide a better grip without sacrificing tool strength or durability.
- **Twists and cuts** soft annealed rebar tie wire.
- **High-leverage design.** Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- **Hook bend handle.**
- **Spring-loaded action** for self-opening.
- **Heavy-duty knurled jaws.**



Pictured: D213-9ST

Line Art: D213-9ST

Cat. No.	Handle Color	Handle Finish	Jaw Length	Jaw Thickness	Jaw Width	Knife Length	Nose Type	Overall Length	Weight (lbs.)
213-9ST	n/a	plain	1-19/32" (41)	5/8" (16)	1-1/4" (32)	25/32" (20)	Square	9-1/4" (235)	1.02

All dimensions are in inches and (millimeters) except where indicated.