

## High Strength 1/4" Wide Steel Fish Tape - 25'

Additional features:

- **Permanent, laser etched 1' increments** on the tape allow you to more accurately measure the depth of conduit runs and determine the amount of tape left to pay out.
- **Polypropylene case and handle** are extremely durable and offer the maximum in shock and impact resistance.
- **Raised finger grips** help transfer 100% of the winding power from your hand and fingers.
- **Round inner ring design** provides a smooth, consistent and comfortable surface for winding and rewinding.
- **The unique sloped handle optimizes** the position of your hand for quick hand-over-hand rewinds and allows a more level payout of tape on the backswing while feeding conduit.
- **Tempered, high quality tape keeps its stability** as it glides between surfaces for effective pushing and pulling of wire under carpets, through insulated walls and over suspended ceilings.
- **25' length is perfect for short wire runs** associated with light commercial, residential and voice-data-video-audio installations.
- **No-snag plastic tip.**
- **Patents: D574,277; 8,212,178; 8,168,921; 8,164,025. Other Patents Pending.**



**Exclusive!  
Laser Etched  
Markings**

Pictured: 56005

Cat. No.	Description	Reel Diameter	Tape Size	Weight (lbs.)
56005	High Strength 1/4" Wide Steel Fish Tape - 25'	7" (178 mm)	25' L x 1/4" W x .030" H (7 m L x 6.3 mm W x .7 mm H)	1.1

All dimensions are in inches and (millimeters) except where indicated.