

High-Tension Hacksaw

- Adjustable blade tension up to 30,000 PSI for fast, precise cuts.
- Soft touch grips.
- Alternative 45 degree mounting for flush cutting.
- Front mount for reciprocating saw blades.
- Convenient blade storage in handle.
- Includes 12" x 24 TPI bi-metal hacksaw blade and 6" x 24TPI bi-metal reciprocating saw blade.



Pictured: 702-12

Cat. No.	Blade Length	Overall Length	Teeth Per Inch	Weight (lbs.)
702-12	12" (305)	18-1/4" (413)	24	1.45

All dimensions are in inches and (millimeters) except where indicated.