



Actual

Catalog Number: BTC5011
Product ID: 7TAH006700R0075
UPC Number: 78378661137
Status: Active

Type BTC - Copper Single-Conductor, One-Hole Mount (Offset-Tang), Conductor Range 1/0 Str-500 kcmil, Length 4-1/4 Inches, Width 1-1/2 Inches, Height 2-21/32 Inches, 13/32 Inch Bolt Hole

- Uniquely designed pressure bar and notched v-bottom collar provide vise-like grip between conductor and terminal.
- Made of electrolytic seamless copper. Screws are zinc-plated steel.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Copper Connectors
Special Features	Uniquely designed pressure bar and notched v-bottom collar provide vise-like grip between conductor and terminal.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	1/0 Str-500 kcmil

Packaging

Inner Quantity	3
Inner Dimensions (inches)	5x4.5x3.2
Outer Quantity	30
Outer Dimensions (inches)	13.2x10.4x6.6
Weight Uom	73 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com