



Actual

**Catalog Number:** **STC0414**  
**Product ID:** 7TAH006710R0025  
**UPC Number:** 78378613422  
**EAN Number:** 05414363161950  
**Status:** Active

Type STC - Copper Single-Conductor, One-Hole Mount (Straight Tang), Conductor Range 14 AWG-4 Str, Length 1-1/4 Inches, Width 1/2 Inch, Height 27/32 Inch

- Uniquely designed pressure bar and notched v-bottom collar provide vise-like grip between conductor and terminal.
- Made of electrolytic seamless copper. Screws are zinc-plated steel.

#### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Copper Connectors
Special Features	Uniquely designed pressure bar and notched v-bottom collar provide vise-like grip between conductor and terminal.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	14 AWG-4 Str

#### Packaging

Inner Quantity	10
Outer Quantity	180
Weight Uom	3 lbs. per 100

#### Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com