

7" Side-Cutting Pliers

- **Custom, US-made tool steel.**
- **Hot-riveted joint** ensures smooth action and no handle wobble.
- **Induction hardened** cutting knives for long life.
- **Unique handle tempering** helps absorb the "snap" when cutting wire.
- **2000 Series** pliers available. Cuts ACSR, screws, nails and most hardened wire.
- **"Handform" handles** for full gripping and cutting power.
- **Precision-hardened plier head** for on-the-job toughness.
- **Sure-gripping** cross-hatched knurled jaws.
- **Plastic-dipped handles*** for comfort and ease of identification.
- ***Journeyman™ pliers available for some styles.**
State-of-the-art, dual-material handles, which provide a better grip without sacrificing tool strength or durability.
- **Sure-gripping, cross-hatched knurled jaws.**



Pictured: D201-8

Line Art: D201-8NE

Cat. No.	Handle Color	Handle Finish	Jaw Length	Jaw Thickness	Jaw Width	Knife Length	Nose Type	Overall Length	Weight (lbs.)
D201-7NE	dark blue	plastic-dipped	1-9/32" (33)	1/2" (13)	1-1/16" (27)	5/8" (16)	New England	7-7/16" (189)	.55

All dimensions are in inches and (millimeters) except where indicated.