

Universal Combination Pliers

JOURNEYMAN

- **State-of-the-art dual material molding process.**
- **Soft material on outer surface** for comfort and a firm grip.
- **Hard, black material** for toughness and durability.
- **Contoured thumb area** for additional comfort and positive feel.
- **Color-coded yellow, dark blue, red, or light blue handles** allow quick identification of tool.
- Custom U.S. steel alloy is forged, precision machined, hardened, carefully tempered and finished in the US by artisans with over 150 years of proprietary world-class manufacturing experience.
- Journeyman tools combine the best of Klein quality and workmanship with the latest in comfort and performance.
- Dual-material Thermoplastic Polyurethane (TPU) grips provide uncompromised performance and durability.
- Universal tapered head design allows greater access in confined spaces.
- Precision machined pipe-grip for greater gripping power.
- Crimping die behind hinge for superior leverage crimping of non-insulated connectors, lugs and terminals.
- Induction hardened cutting knives for long life.
- Hot riveted joint ensures smooth action and no handle wobble.
- Sure-gripping cross-hatched knurled jaws.
- Unique handle tempering helps absorb the "snap" when cutting wire.



Pictured: J12098

Cat. No.	Handle Color	Handle Finish	Jaw Length	Jaw Thickness	Jaw Width	Knife Length	Nose Type	Overall Length	Weight (lbs.)
J12098	Dark Blue/Black	Journeyman	1-25/32" (45)	17/32" (13)	1-1/32" (26)	3/4" (19)	Universal	8-3/4" (222)	1.13

All dimensions are in inches and (millimeters) except where indicated.