



Home » Catalog » Holemaking Products & Accessories » Hole Saws » Bi-Metal Hole Saws

7/8" (22 mm) Bi-Metal Hole Saw



Cat. No. 31514

Product Features

Cuts through steel, wood, plastic, stainless steel, and cast iron.
Rugged cobalt bi-metal construction for maximum longevity.
Deep cup cuts through studs in one pass.
Variable pitch teeth cut faster and smoother while reducing chatter.
Longer lasting design for more cuts per saw .
Multiple knock-out slots and holes for easy core removal.
Note: Set pilot drill point 1/8" (3 mm) beyond toothpoints.

BUY NOW

FIND RETAILER

Specifications

Downloads

Warnings

Pipe Tap Size: 3/4" (19 mm)
Saw Diameter: 7/8" (22 mm)

Pipe Entr. Size: 1/2" (13 mm)
Weight (lbs.): .60

For Use with Arbor No.: 31650, 31655, 31660

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)

