

# Pocket Knives – One Blade

## Lightweight Lockback Knives

- Blades are AUS 8 stainless steel hardened to 58-59 Rc.
- Premium quality blade offers superior edge holding.
- Impact-resistant nylon resin handle with rubber insert (Cat. Nos. 44002-44005).
- Slim and comfortable silver anodized-aluminum handle for corrosion-resistance (Cat. Nos. 44000, 44001, 44006, 44007).
- Black chrome blade and black anodized-aluminum handle for corrosion-resistance (Cat. Nos. 44000-BLK and 44001-BLK).
- Reversible thumb stud provides easy one-handed opening.



44001-BLK



44001



44002



44005

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
<b>Drop Point Blade</b>				
44000	AUS 8 stainless steel	2-1/4" (57 mm)	3-1/8" (76 mm)	1.5
44000-BLK	AUS 8 stainless steel	2-1/4" (57 mm)	3-1/8" (76 mm)	1.1
44001*	AUS 8 stainless steel	2-1/2" (64 mm)	3-1/2" (89 mm)	2.5
44001-BLK*	AUS 8 stainless steel	2-1/2" (64 mm)	3-1/2" (89 mm)	1.3
44002	AUS 8 stainless steel	2-3/8" (60 mm)	3-1/2" (89 mm)	1.5
44003	AUS 8 stainless steel	2-3/4" (70 mm)	4-1/8" (105 mm)	2.5
<b>Sheepfoot Blade</b>				
44004	AUS 8 stainless steel	2-3/8" (60 mm)	3-1/2" (89 mm)	1.5
44005	AUS 8 stainless steel	2-5/8" (67 mm)	4-1/8" (105 mm)	2.5
44006*	AUS 8 stainless steel	2-5/8" (67 mm)	3-1/2" (89 mm)	1.3
<b>Coping Blade</b>				
44007*	AUS 8 stainless steel	2-1/2" (63 mm)	3-1/2" (89 mm)	1.5

\* Includes a pocket/belt clip.

## Lightweight Lockback Knives – Tanto Blade

- Tanto blade is AUS 8 stainless-steel hardened to 58-59 Rc.
- Black chrome blade and black anodized-aluminum handle for corrosion resistance.
- Premium quality blade offers superior edge holding.
- Reversible thumb stud provides easy, one-handed opening.
- Includes a pocket/belt clip.



44052BLK

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
44052BLK	AUS 8 stainless-steel	2-3/4" (69 mm)	3-5/8" (92 mm)	2.4

