

50549 replacement blade

3-1/4" (83 mm) .08 lbs. (0.03 kg)

50549

## Ratcheting PVC-Cutter

- Makes clean, burr-free cuts through PVC.
- High-leverage ratchet-action for maximum cutting power.
- Easy one-hand cutting.
- Special heat-treated blades stay sharp longer and reduce pipe deformation.
- Hooked jaw holds pipe in proper cutting position.



Cat. No.	PVC Cutting Capacity	Non-metallic Tubing Cutting Capacity	Length	Weight
50500	1/2" - 1-1/4"	1" (19 mm)	9" (229 mm)	1.1 lbs. (0.5 kg)
<b>Replacement Parts</b>				
50503	replacement blade		4" (102 mm)	.19 lbs. (0.08 kg)
50511	replacement spring		2-3/8" (60 mm)	.006 lbs. (0.002 kg)

## Large Capacity Ratcheting PVC-Cutter

- Makes clean, burr-free cuts through PVC.
- High-leverage ratchet-action for maximum cutting power.
- Special heat-treated blades stay sharp longer and reduce pipe deformation.
- Handle latch keeps tool closed.



Cat. No.	PVC Cutting Capacity	Non-metallic Tubing Cutting Capacity	Length	Weight
50501	1/2" - 2"	1" (19 mm)	16-1/2" (419 mm)	2.6 lbs. (1.2 kg)
<b>Replacement Parts</b>				
50504	replacement blade		5-3/4" (146 mm)	.53 lbs. (0.24 kg)
50512	replacement spring		2-3/8" (60 mm)	.01 lbs. (0.004 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.

**▲WARNING:** Always wear approved eye protection.

**▲WARNING:** NEVER use on or near live electrical circuits.

**▲WARNING:** Do NOT use to cut metallic pipes or cable wire.

**▲WARNING:** Do NOT cut cold PVC.

