

Adjustable Wrenches

Adjustable Wrenches – Standard Capacity

Additional Features:

- Forged heat-treated alloy steel for maximum strength and light weight.
- High-polish chrome finish.



506-15

Cat. No.	Handle Color	Handle Finish	Length	Capacity	Weight (lbs.)
D506-4	transparent red	plastic-dipped	4-1/2" (114 mm)	1/2" (12 mm)	.13
506-15	-	high-polish chrome	15-7/8" (403 mm)	1-11/16" (42 mm)	2.92
500-18	-	high-polish chrome	18-1/4" (463 mm)	2-1/16" (52 mm)	4.67
500-24	-	high-polish chrome	24" (610 mm)	2-1/2" (63 mm)	7.76

Adjustable-Head Construction Wrenches

- Versatile wrench fits nuts and bolts to 1-1/2" (38 mm).
- Eliminates the need to carry several fixed-size wrenches.
- Forged from select alloy steel with continuous-taper handle.
- Industrial black finish for corrosion resistance.
- Handy lanyard hole (Cat. No. 3227).
- Fits nuts and bolts to 1-5/16" (33 mm) (Cat. No. 3227).



3239



3227

Cat. No.	Max. Size Capacity	Length	Weight (lbs.)
3239	1-1/2" (38 mm)	16" (406 mm)	2.36
3227	1-5/16" (33 mm)	11" (279 mm)	1.20

All dimensions are in inches and (millimeters).

▲WARNING: Always wear approved eye protection.

▲WARNING: Do NOT push or hammer wrench.

▲WARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

▲WARNING: Do NOT extend handle length.

